Glass-Cup

ISCUP-G 80x40x30 Cup 2

Part no..:10.01.15.00393

https://www.schmalz.com/10.01.15.00393

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Innospann Clamping Equipment ISCUP/ISMB/ISQB > ISCUP-G 80x40x30 Cup 2

Suction Glas-cup for Innospann



- Dimensions (LxB): 80 x 40
- Length L: 80 mm
- Width B: 40 mm
- Height H: 30 mm

Design Data

Attribute	Value
B	40 mm
H	30 mm
L	80 mm

Technical Data

Attribute	Value
Weight	0.10 kg


Spare parts

Glass-Cup

ISCUP-G 80x40x30 Cup 2

Part no..:10.01.15.00393

https://www.schmalz.com/10.01.15.00393



DI-PROF 4x10 MOS EPDM HR

Part no..:10.01.15.00062

Width B: 4 mm
Height H: 10 mm
Sealing material: EPDM
Material type: Foam rubber
Form: half-round



ISDR 81x43x12 Cup 2 NBR-50

Part no..:10.01.15.00418

Length L: 81 mm
Width B: 43 mm
Height H: 12 mm