Flat suction cup (round)

SUF 15 NBR-55 G1/8-AG

Part no..:10.01.01.14113

https://www.schmalz.com/10.01.01.14113


Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups SUF > SUF 15 NBR-55 G1/8-AG

Flat suction cup (round) for process safe handling of smooth or slightly rough surfaces



- Size: 15
- Suction cup material: Nitrile rubber NBR
- Material hardness [Shore A]: 55 Shore A
- Vacuum connection: G1/8"-M

Design Data



Attribute	Value
Dmax(S)	16.80 mm
Ds	15 mm
dn	3.10 mm
G1	G1/8"-M
H	15 mm
LG1	7.50 mm
SW1	14 mm
Z (Stroke)	1.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	9 N
Pull-off force	9 N
Volume	0.22 cm^3
Curve radius (min) (convex)	20 mm
Hose diameter (rec.) d	4 mm
Size	15
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A

Contact Schmalz
J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-105 | kundencenter@schmalz.de

Flat suction cup (round)

SUF 15 NBR-55 G1/8-AG

Part no..:10.01.01.14113

https://www.schmalz.com/10.01.01.14113

Weight	4.70 g
Product family	SUF
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SC 030 G1/8-AG

Part no..:10.01.06.04288

Connection geometry: 030
Vacuum connection: G1/8"-M
Fitting length: 6 mm
Nominal diameter dn: 3.1 mm



SUF 15 NBR-55 SC030

Part no..:10.01.01.13945

Size: 15
Suction cup material: Nitrile rubber NBR
Material hardness [Shore A]: 55 Shore A