# Tooling-System-Schmalz-Ejector


SEAC 10 RP VS-T R

Part no..:10.02.02.03290

https://www.schmalz.com/10.02.02.03290


Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Decentralized Ejectors > Ejectors With Blow Off System SEAC RP > SEAC 10 RP VS-T R

## Tooling-System-Schmalz-Ejektor



- Nozzle diameter: 1 mm
- Function: pneumatic air-saving function
- Add. function: electronic vacuum switch
- construction shape compact ejectors: Version right
- Pressure range (operating pressure): 4.0 ... 6.0 bar

## Design Data




| Attribute | Value |
|---|---|
| B | 44.50 mm |
| B3 | 14.20 mm |
| d | 4.30 mm |
| d1 | 13.80 mm |
| D | 27 mm |
| G1 | G1/8"-F |
| G3 | M8-M |
| G4 | G1/8"-F |
| H | 38.30 mm |
| H1 | 39.80 mm |
| H2 | 29.30 mm |
| L | 52 mm |
| L1 | 88.10 mm |
| L2 | 29.50 mm |
| L3 | 8 mm |
| L4 | 22 mm |
| X1 | 28 mm |

## Technical Data

| Attribute | Value |
|---|---|

# Tooling-System-Schmalz-Ejector

SEAC 10 RP VS-T R

Part no..:10.02.02.03290

https://www.schmalz.com/10.02.02.03290

| | |
|---|---|
| Nozzle diameter | 1 mm |
| Degree of evacuation | 85 % |
| Suction rate (max.) | 36 l/min |
| Suction rate (max.) | 2.10 m³/h |
| Air consumption suction | 65 l/min |
| Air consumption suction | 3.90 m³/h |
| Max. air consumption blow off | 92 l/min |
| Pressure range (operating pressure) | 4.0 ... 6.0 bar |
| Weight | 180 g |
| Pressure range (operating pressure) | 58.0 ... 87.0 |
| Suction rate (max.) | 1.27 cfm |
| Air consumption suction | 2.30 cfm |
| Air consumption blow off | 3.18 cfm |
| Max. vacuum | 25.10 inHg |
| Product family | SEAC-RP |

Note: Air consumption: At optimal operating pressure (4,5 bar)

## Accessories



**ASK B-M8-4 5000 K-4P**

Part no..:10.06.02.00031

| |
|---|
| Electrical connection: Fem connect M8, 4 pol |
| Cable length: 5,000 mm |
| Material hose: PUR cable |

# Tooling-System-Schmalz-Ejector

SEAC 10 RP VS-T R

Part no..:10.02.02.03290

https://www.schmalz.com/10.02.02.03290



**ADP-EJ 45.5x21x44-G1/4-IG SEAC VA-S**

Part no..:10.02.02.03483

| |
|---|
| Length L: 45.5 mm |
| Width B: 21 mm |
| Height H: 44 mm |
| Thread G1: G1/4"-F |
| Construction use: Compact ejectors SEAC |



**ADP-EJ 45.5x21x44-G1/4-IG SEAC VA-L**

Part no..:10.02.02.03484

| |
|---|
| Length L: 45.5 mm |
| Width B: 21 mm |
| Height H: 44 mm |
| Thread G1: G1/4"-F |
| Construction use: Compact ejectors SEAC |



**ADP-EJ 38x20x11-G1/4-IG SEAC**

Part no..:10.02.02.04067

| |
|---|
| Length L: 38 mm |
| Width B: 20 mm |
| Height H: 11 mm |
| Thread G1: G1/4"-F |
| Construction use: Compact ejectors SEAC |

# Tooling-System-Schmalz-Ejector

SEAC 10 RP VS-T R

Part no..:10.02.02.03290

https://www.schmalz.com/10.02.02.03290



**ADP-EJ 38x20x11-G1/8-IG SEAC**

Part no..:10.02.02.04068

| |
|---|
| Length L: 38 mm |
| Width B: 20 mm |
| Height H: 11 mm |
| Thread G1: G1/8"-F |
| Construction use: Compact ejectors SEAC |