Bellows suction cup (round)

SPB4 20 SI-55 G1/4-AG

Part no..:10.01.06.03515

https://www.schmalz.com/10.01.06.03515


Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for the Packaging Industry > Bellows Suction Cups SPB4 (4.5 Folds) > SPB4 20 SI-55 G1/4-AG

Bellows suction cup (round) for very uneven workpieces



- Size: 20
- Suction cup material: Silicone SI
- Material hardness [Shore A]: 55 Shore A
- Thread G1: G1/4"-M
- Number of folds: 4.5

Design Data



Attribute	Value
d2	13.50 mm
dn	8 mm
Dmax(S)	24.40 mm
Ds	21.40 mm
G1	G1/4"-M
H	48.40 mm
LG1	10 mm
SW1	22 mm
Z (Stroke)	10 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	8 N
Pull-off force	11 N
Volume	7.90 cm³
Hose diameter (rec.) d	9 mm
Number of folds	4.50
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A
Size	20

Bellows suction cup (round)

SPB4 20 SI-55 G1/4-AG

Part no..:10.01.06.03515

https://www.schmalz.com/10.01.06.03515

Weight	20.70 g
Product family	SPB4

Accessories



SIEB 17x0.8 MS-A2 103 0.103/0.07

Part no..:10.07.01.00320


- External diameter D: 17 mm
- Length L: 0.8 mm
- Material: Brass / Stainless steel
- Filter pore size: 103 µm



SSB 16-27 ST-VZ

Part no..:10.07.10.00002

- Clamping range: 16.0 ... 27.0 mm
- Material: Steel
- Surface: galvanised



SPI 16 PE SPB4-20

Part no..:10.01.06.02915

- Size: 16
- Material: Polyethylene
- Use: SPB4-20

Bellows suction cup (round)

SPB4 20 SI-55 G1/4-AG

Part no..:10.01.06.03515

https://www.schmalz.com/10.01.06.03515

Spare parts



SC 080 G1/4-AG

Part no..:10.01.06.03268

Connection geometry: 080
Vacuum connection: G1/4"-M
Length L1: 32 mm
Fitting length: 7.5 mm
Nominal diameter dn: 8 mm



SPB4 20 SI-55 SC080

Part no..:10.01.06.02588

Size: 20
Suction cup material: Silicone SI
Material hardness [Shore A]: 55 Shore A
Number of folds: 4.5