Flat suction cup (round)

SUF 15 NBR-55 M5-AG

Part no..:10.01.01.14155


https://www.schmalz.com/10.01.01.14155

Flat suction cup (round) for process safe handling of smooth or slightly rough surfaces



- Size: 15
- Suction cup material: Nitrile rubber NBR
- Material hardness [Shore A]: 55 Shore A
- Vacuum connection: M5-M

Design Data



Attribute	Value
Dmax(S)	16.80 mm
Ds	15 mm
dn	1.80 mm
G1	M5-M
H	13.90 mm
LG1	4.70 mm
SW1	8 mm
Z (Stroke)	1.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	9 N
Pull-off force	9 N
Volume	0.22 cm³
Curve radius (min) (convex)	20 mm
Hose diameter (rec.) d	4 mm
Size	15
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A

Contact Schmalz
Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Flat suction cup (round)

SUF 15 NBR-55 M5-AG

Part no..:10.01.01.14155

https://www.schmalz.com/10.01.01.14155

Weight	1.90 g
Product family	SUF
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SC 030 M5-AG

Part no..:10.01.06.02802

Connection geometry: 030
Connection: M5-M
Length L1: 15.5 mm
Fitting length: 5 mm
Nominal diameter dn: 1.8 mm



SUF 15 NBR-55 SC030

Part no..:10.01.01.13945

Size: 15
Suction cup material: Nitrile rubber NBR
Material hardness [Shore A]: 55 Shore A