Suction plate (round)

SPL-HT 190 FPM-F-65

Part no..:10.01.01.00834

https://www.schmalz.com/10.01.01.00834


Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for High-Temperature Applications > SPL-HT 190 FPM-F-65

Suction plate for high-temperature applications



- Size: 190
- Suction cup material: Fluorocaoutchuc FPM-F
- Material hardness [Shore A]: 65 Shore A
- Working temperature max.: 350 °C

Design Data



Attribute	Value
d	40 mm
Dmax(S)	209 mm
Ds	190 mm
H	17 mm
Z (Stroke)	8 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	1050 N
Curve radius (min) (convex)	350 mm
Size	190
Working temperature max.	350 °C
Suction cup material	Fluorocaoutchuc FPM-F
Weight	256 g
Product family	SPL-HT

Contact Schmalz
Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in

Suction plate (round)

SPL-HT 190 FPM-F-65

Part no..:10.01.01.00834

https://www.schmalz.com/10.01.01.00834