Bellows suction cup HT2 (round)

SAB 60 HT2-65 G3/8-IG

Part no..:10.01.06.03354

https://www.schmalz.com/10.01.06.03354


Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups SAB HT2 (1.5 Folds) > SAB 60 HT2-65 G3/8-IG

Bellows suction cup (round) for handling hot workpieces



- Size: 60
- Suction cup material: High temperature material HT2
- Material hardness [Shore A]: 65 Shore A
- Temperature resistance: 200 °C
- Nipple material: Aluminum
- Connection: G3/8-IG
- Number of folds: 1.5

Design Data



Attribute	Value
dn	6 mm
D1	49.50 mm
Dmax(S)	67 mm
Ds	61.20 mm
G1	G3/8"-F
H	41.30 mm
LG1	15 mm
SW1	22 mm
Z (Stroke)	14.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	82 N
Pull-off force	136 N
Lateral force	126 N
Volume	32 cm^3
Curve radius (min) (convex)	30 mm
Hose diameter (rec.) d	6 mm
Size	60
Connection	G3/8"-F

Contact Schmalz
Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in

Bellows suction cup HT2 (round)

SAB 60 HT2-65 G3/8-IG

Part no..:10.01.06.03354

https://www.schmalz.com/10.01.06.03354

Suction cup material	High temperature material HT2
Material hardness [Shore A]	65 Shore A
Weight	51.50 g
Number of folds	1.50
Product family	SAB

Contact Schmalz
Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 |
schmalz@schmalz.co.in