Suction cup (round)

SAUG-SCGS 40 SI-HD-65

Part no..:10.01.30.00918

https://www.schmalz.com/10.01.30.00918


Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Flow Grippers > Suction Cups for Flow Grippers SCGS > SAUG-SCGS 40 SI-HD-65

Suction cup (round)



- Size: 40
- Suction cup material: Silicone SI-HD
- Material hardness [Shore A]: 65 Shore A

Design Data



Attribute	Value
D1	41 mm
Dmax (N)	25 mm
Dmax(S)	41.50 mm
dn	18.90 mm
Ds	40.50 mm
G1	M20x1-F
H	27.80 mm
LG1	5 mm
Z (Stroke)	3.70 mm

Technical Data

Attribute	Value
Size	40
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65 Shore A
Weight	21.20 g
Product family	SAUG-SCGS

Contact Schmalz
Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | schmalz@schmalz.co.in

Suction cup (round)

SAUG-SCGS 40 SI-HD-65

Part no..:10.01.30.00918

https://www.schmalz.com/10.01.30.00918

Spare parts



FLSA 40 SI-HD-65

Part no..:10.01.06.03886

Size: 40
Suction cup material: Silicone SI-HD
Material hardness [Shore A]: 65 Shore A