
Flat suction cup (round)

SUF 60 HT1-60 G1/4-IG

Part no..:10.01.01.14082


https://www.schmalz.com/10.01.01.14082

Flat suction cup (round) for process safe handling of smooth or slightly rough surfaces



- Size: 60
- Suction cup material: High temperature material HT1
- Material hardness [Shore A]: 60 Shore A
- Vacuum connection: G1/4"-F

Design Data



Attribute	Value
Dmax(S)	66.40 mm
Ds	60 mm
dn	5.10 mm
G1	G1/4"-F
H	33.90 mm
LG1	12 mm
SW1	17 mm
Z (Stroke)	5.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	140 N
Pull-off force	140 N
Volume	12.70 cm^3
Curve radius (min) (convex)	75 mm
Hose diameter (rec.) d	6 mm
Size	60
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A

Contact Schmalz
Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 | schmalz@schmalz.it

Flat suction cup (round)

SUF 60 HT1-60 G1/4-IG

Part no..:10.01.01.14082

https://www.schmalz.com/10.01.01.14082

Weight	40.30 g
Product family	SUF
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m