Spring plunger

FSTIm M3-IG 4/2.5 A 5 IN

Part no..:10.01.02.01333

https://www.schmalz.com/10.01.02.01333


Home > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Spring Plungers > Spring Plungers FSTIm > FSTIm M3-IG 4/2.5 A 5 IN

Spring plunger with internal damping spring and height compensation



- Suction cup connection: M3-F
- Vacuum connection: Hose 4/2.5
- Shape: Axial vacuum guide
- Spring stroke Z: 5 mm
- Shape mounting elements: (electrically) insulating

Design Data



Attribute	Value
dn	1.30 mm
G2	M3-F
G3	M10x1-M
H	40.70 mm
H2	14 mm
LG2	4.50 mm
LG3	19 mm
SW1	14 mm
SW2	8 mm
Z (Stroke)	5 mm

Recommendation: Avoid maximum plunger stroke Z during continuous operation to extend service life Ensure that the hose guide is free from distortion

Technical Data

Attribute	Value
Shape mounting elements	(electrically) insulating
Spring rate	0.06 N/mm
Spring pretension	0.50 N
Spring force, center	0.64 N
Vertical load	15 N
Horizontal load	10 N

Spring plunger

FSTIm M3-IG 4/2.5 A 5 IN


Part no..:10.01.02.01333

https://www.schmalz.com/10.01.02.01333

Weight	14 g
Operating temperature	0 ... 80 °C
Product family	FSTIm

Note: Spring force: Referred to 50 % of operating stroke Vertical loading: Maximum static loading Horizontal load: The specification of the horizontal load refers to the lower edge of the plunger with extended spring. It is a maximum static stress and it impairs the spring compression and extensionin horizontal position.

Accessories



VSL 4-2.5 PU BL SO

Part no..:10.07.09.00142



HTR-STA 47 1N D10/16 FL

Part no..:10.08.03.00085

Length L: 47 mm
Connection 1: Sliding block
Connection of suction cup, spring plunger: Contour D10 and D16
Shape: flat

Spring plunger

FSTIm M3-IG 4/2.5 A 5 IN

Part no..:10.01.02.01333

https://www.schmalz.com/10.01.02.01333



HTR-STS 30x30 D10/16 WI

Part no..:10.08.03.00088

Connection 1: 30x30
Connection of suction cup, spring plunger: Contour D10 and D16
Shape: angled



HTR-STS 40x40 D10/16 WI

Part no..:10.08.03.00089

Connection 1: 40x40
Connection of suction cup, spring plunger: Contour D10 and D16
Shape: angled