Bellows suction cup HT1 (round)


SAB 40 HT1-60 G1/4-IG

Part no..:10.01.06.02724

https://www.schmalz.com/10.01.06.02724


Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Glass > Bellows Suction Cups SAB HT1 (1.5 Folds) > SAB 40 HT1-60 G1/4-IG

Bellows suction cup (round) for markless handling of workpieces



- Size: 40
- Suction cup material: High temperature material HT1
- Material hardness [Shore A]: 60 Shore A
- Nipple material: Aluminum
- Connection: G1/4-IG
- Number of folds: 1.5

Design Data



Attribute	Value
dn	4 mm
D1	32 mm
Dmax(S)	45 mm
Ds	40.10 mm
G1	G1/4"-F
H	28.80 mm
LG1	12 mm
SW1	17 mm
Z (Stroke)	10 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	38 N
Pull-off force	59 N
Lateral force	36 N
Lateral force (oily surface)	33 N
Volume	7 cm^3
Curve radius (min) (convex)	40 mm
Hose diameter (rec.) d	4 mm
Size	40

Bellows suction cup HT1 (round)

SAB 40 HT1-60 G1/4-IG

Part no..:10.01.06.02724

https://www.schmalz.com/10.01.06.02724

Number of folds	1.50
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A
Weight	14.30 g
Product family	SAB

Contact Schmalz
Schmalz S.r.l. a Socio Unico | Via Ticino 105, 28066 Galliate (NO), Italy | +39 0321 62 15 10 |
schmalz@schmalz.it