Multi-Clamp - Suction plate

VC-M-SP 160x160x30

Part no..:10.01.12.01836

https://www.schmalz.com/10.01.12.01836


Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Manual Work > Multi-Clamp Suction Plates VC-M-SP / VC-M-SPV > VC-M-SP 160x160x30

Multi-Clamp - Suction plate with integrated vacuum generation



- Length L: 160 mm
- Width B: 160 mm
- Height H: 30 mm
- Air consumption: 48 l/min
- Air consumption: 2.88 m³/h
- Suction rate: 2.3 m³/h

Design Data



Attribute	Value
B	160 mm
H	30 mm
d	6 mm
L	160 mm

Technical Data

Attribute	Value
Weight	0.88 kg

Accessories

Multi-Clamp - Suction plate

VC-M-SP 160x160x30

Part no..:10.01.12.01836

https://www.schmalz.com/10.01.12.01836



DI-PROF 8x10.5 MOS EPDM-15

Part no..:10.01.12.02056



REIB-INS 8.1x18 VC-M

Part no..:10.01.12.02000

Construction use: Multi-Clamp



VC-M-B 170x165x209

Part no..:10.01.12.01854

Length L: 170 mm

Width B: 165 mm

Height H: 209 mm

Spare parts

Multi-Clamp - Suction plate

VC-M-SP 160x160x30

Part no..:10.01.12.01836

https://www.schmalz.com/10.01.12.01836



REIB-INS 8.1x18 VC-M

Part no..:10.01.12.02000

Construction use: Multi-Clamp



DI-PROF 8x10.5 MOS EPDM-15

Part no..:10.01.12.02056