Bellows suction cups (round)

FSGA 25 NK-45 G1/8-AG

Part no..:10.01.06.00405

https://www.schmalz.com/10.01.06.00405


Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups FSGA (1.5 Folds) > FSGA 25 NK-45 G1/8-AG

Bellows suction cup (round) with optimal adaptation to uneven surfaces



- Size: 25
- Suction cup material: Natural Rubber NK
- Material hardness [Shore A]: 45 Shore A
- Nipple material: Aluminum
- Connection: G1/8"-M
- Number of folds: 1.5
- Vacuum connection: G1/8"-M

Design Data



Attribute	Value
d2	9.90 mm
Dmax(S)	26.50 mm
dn	3.50 mm
Ds	22.50 mm
G1	G1/8"-M
H	29 mm
LG1	7.50 mm
SW1	14 mm
Z (Stroke)	9 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction cup material	Natural Rubber NK
Material hardness [Shore A]	45 Shore A
Size	25
Number of folds	1.50
Connection	G1/8-AG
Curve radius (min) (convex)	25 mm
Volume	2.94 cm³

Contact Schmalz
Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8026 2403
schmalz@schmalz.co.kr

Bellows suction cups (round)

FSGA 25 NK-45 G1/8-AG

Part no..:10.01.06.00405

https://www.schmalz.com/10.01.06.00405

Suction force (-600mbar)	5.30 N
Pull-off force	17.30 N
Hose diameter (rec.) d	4 mm
Weight	6.40 g
Product family	FSGA

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N016 G1/8-AG DN350

Part no..:10.01.06.05735

Nipple family: N 016
Thread G1: G1/8"-M
Length L1: 20 mm
Fitting length: 6 mm
Nominal diameter dn: 3.5 mm
Material: Aluminum



FGA 25 NK-45 N016

Part no..:10.01.06.00378

Size: 25
Suction cup material: Natural Rubber NK
Material hardness [Shore A]: 45 Shore A
Number of folds: 1.5

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8776 2403

schmalz@schmalz.co.kr