Compact ejector

SCPSi-UHV-HD 07 G02 NO

Part no..:10.02.02.06292

https://www.schmalz.com/10.02.02.06292

Compact ejector with special nozzle technology for increased vacuum level and IO-Link functionality



- construction shape compact ejectors: HD
- Nozzle diameter: 0.7 mm
- Connection: G1/8"(1)-G1/8"(2)
- Electrical connection: Male connect M12, 5 pol
- Suction rate (max.): 13 l/min
- Air consumption suction: 17.2 l/min
- Sound level free: 62 dB(A)
- Pressure range (operating pressure): 3.0 ... 6.0 bar
- Max. vacuum: -910 mbar
- Control valve: Normally open
- Function: Digital air-saving function
- Protection type IP: IP 65 (with plug)

Design Data


Contact Schmalz
Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8026 2403
schmalz@schmalz.co.kr

Compact ejector

SCPSi-UHV-HD 07 G02 NO

Part no..:10.02.02.06292

https://www.schmalz.com/10.02.02.06292



Attribute	Value
B	18 mm
B1	18.60 mm
D	16.50 mm
d	4.40 mm
D2	9 mm
d3	2.60 mm
G1	G1/8"-F
G2	G1/8"-F
G3	M12x1-M
H	99 mm
H2	40.80 mm
H3	47.50 mm
H4	16.50 mm
H5	5.50 mm
H6	31.50 mm
L	135 mm
L1	150 mm
L2	91.50 mm
L3	22 mm
L4	31 mm
L5	83.80 mm
X1	36.90 mm
X2	16 mm
Y1	12 mm
Y2	12 mm

Technical Data

Attribute	Value
Nozzle size	07
Degree of evacuation	91 %
Suction rate (max.)	13 l/min
Suction rate (max.)	0.80 m³/h
Air consumption suction	17.20 l/min
Air consumption suction	1 m³/h
Air consumption blow off	7.20 m³/h
Sound level free	62 dB(A)
Sound level suction	64 dB(A)
Pressure range (operating pressure)	3.0 ... 6.0 bar

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8 6 2403

schmalz@schmalz.co.kr

Compact ejector

SCPSi-UHV-HD 07 G02 NO

Part no..:10.02.02.06292

https://www.schmalz.com/10.02.02.06292

Connection	G02
Control valve	Normally open
Electrical connection	M12-5
Weight	0.21 kg
Max. air consumption blow off	120 l/min
Operating temperature	0 ... 50 °C
Pressure range (operating pressure)	43.5 ... 87.0
Air consumption blow off	4.24 cfm
Air consumption suction	0.61 cfm
Suction rate (max.)	0.46 cfm
Max. vacuum	-26.87 inHg
Product family	SCPSi-UHV-HD

Accessories



ASK B-M12-5 5000 K-5P

Part no..:21.04.05.00080

Electrical connection: Fem connect M12, 5 pol
Cable length: 5,000 mm
Material hose: PUR cable



ASK B-M12-5 1000 S-M12-5

Part no..:21.04.05.00158

Pressure range (operating pressure): bar
Electrical connection: Fem connect M12, 5 pol
Cable length: 1,000 mm
Material hose: PUR cable

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8026 2431

schmalz@schmalz.co.kr

Compact ejector

SCPSi-UHV-HD 07 G02 NO

Part no..:10.02.02.06292

https://www.schmalz.com/10.02.02.06292



ASK B-M12-5 2000 S-M12-5

Part no..:21.04.05.00211

Pressure range (operating pressure): bar
Electrical connection: Fem connect M12, 5 pol
Cable length: 2,000 mm
Material hose: PUR cable



ASV SM/CPi B-M12-5 2xS-M12-4

Part no..:10.02.02.03490

Pressure range (operating pressure): bar
Length L: 1,050 mm



HUT-SN-KL 75x18x9 SCPS

Part no..:10.02.02.04149

Length L: 75 mm
Width B: 18 mm
Height H: 9 mm
Construction use: Compact ejectors SCPS/SCPSi

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8026 2403

schmalz@schmalz.co.kr

Compact ejector

SCPSi-UHV-HD 07 G02 NO

Part no..:10.02.02.06292

https://www.schmalz.com/10.02.02.06292



VFI CN6/4 50

Part no..:10.07.01.00241

Connection: Hose 6/4 with Cap nut

Filter pore size: 50 µm



VFI 6/4 50

Part no..:10.07.01.00328

Connection: Hose 6/4

Filter pore size: 50 µm

Spare parts



SD 16.5x51 SCPS

Part no..:10.02.02.05094

External diameter D: 16.5 mm

Length L: 51 mm

Construction use: Compact ejectors SCPS/SCPSi

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8026 2051

schmalz@schmalz.co.kr

Compact ejector

SCPSi-UHV-HD 07 G02 NO

Part no..:10.02.02.06292

https://www.schmalz.com/10.02.02.06292



VACU-SET 07 12.80x76.60 SCPS

Part no..:10.02.02.06259

- Nozzle size: 0.7 mm
- External diameter D: 12.8 mm
- Length L: 76.6 mm
- Construction use: Compact ejectors SCPS/SCPSi

WART SCPS/SCPSi-HD

Part no..:10.02.02.06343

- Construction use: Compact ejectors SCPS/SCPSi
- Size: HD

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 876 2403

schmalz@schmalz.co.kr