Hose clamp

SSD 43-48 ST-VZ

Part no..:10.07.10.00020

https://www.schmalz.com/10.07.10.00020


Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Hose Clamps SSB / SSD > SSD 43-48 ST-VZ

Hose clamp for securing wire-reinforced hoses



- Clamping range: 43.0 ... 48.0 mm
- Material: Steel
- Surface: galvanised

Design Data



Attribute	Value
d1	43 mm
d2	48 mm
L	15 mm

Technical Data

Attribute	Value
Clamping range	43.0 ... 48.0 mm
Material	Steel
Weight	27 g
Product family	SSB / SSD

Contact Schmalz
Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8026 2403
schmalz@schmalz.co.kr

Hose clamp

SSD 43-48 ST-VZ

Part no..:10.07.10.00020

https://www.schmalz.com/10.07.10.00020

Accessories



VSL 48-38 PU-DS-AS TR

Part no..:10.07.09.00031

External diameter D: 48 mm
Internal diameter d: 38 mm
Length max.: 20 m
Material hose: PU, wire spiral, antistatic
Bending radius min.: 29 mm
Pressure range (operating pressure): -1.00 ... 3.21 bar
Operating temperature: -40 ... 90 °C



VSL 49-38 PU-DS-AS TR

Part no..:10.07.09.00052

External diameter D: 49 mm
Internal diameter d: 38 mm
Length max.: 15 m
Material hose: PU, wire spiral, antistatic
Bending radius min.: 104 mm
Pressure range (operating pressure): -1.00 ... 4.47 bar
Operating temperature: -20 ... 90 °C



VSL 48-40 PVC-PS GR

Part no..:10.07.09.00011

External diameter D: 48 mm
Internal diameter d: 40 mm
Length max.: 50 m
Material hose: PVC with PVC-spiral
Bending radius min.: 70 mm
Pressure range (operating pressure): -0.49 ... 1.00 bar
Operating temperature: -20 ... 70 °C

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 8026 2121

schmalz@schmalz.co.kr