Flat suction cup (round)

PFYN 40 FPM-65 G1/8-AG

Part no..:10.01.01.00188


https://www.schmalz.com/10.01.01.00188

Flat suction cup (round) for smooth or slightly rough surfaces



- Size: 40
- Suction cup material: Fluorocaotchuc FPM
- Material hardness [Shore A]: 65 Shore A
- Material property: non-marking
- Nipple material: Aluminum
- Vacuum connection: G1/8"-M

Design Data



Attribute	Value
dn	2.40 mm
Dmax(S)	43 mm
Ds	40 mm
G1	G1/8"-M
H	19 mm
LG1	8 mm
SW1	14 mm
Z (Stroke)	3.50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	57.70 N
Volume	3.80 cm^3
Curve radius (min) (convex)	50 mm
Hose diameter (rec.) d	4 mm
Size	40
Suction cup material	Fluorocaotchuc FPM
Material hardness [Shore A]	65 Shore A

Contact Schmalz
Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | +52 442 209 52
schmalz@schmalz.com.mx

Flat suction cup (round)

PFYN 40 FPM-65 G1/8-AG

Part no..:10.01.01.00188

https://www.schmalz.com/10.01.01.00188

Weight	14.70 g
Product family	PFYN
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SU 40

Part no..:10.01.01.12856

Size: 40
Clamping range: 35.0 ... 45.0 mm
Temperature resistance: 80 °C

Spare parts



SA-NIP N007 G1/8-AG DN240

Part no..:10.01.01.03531

Nipple family: N 007
Thread G1: G1/8"-M
Length L1: 21 mm
Length L: 5 mm
Fitting length: 5 mm
Nominal diameter dn: 2.4 mm
Material: Aluminum
Spanner size SW2: 4 mm

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52

schmalz@schmalz.com.mx

Flat suction cup (round)

PFYN 40 FPM-65 G1/8-AG

Part no..:10.01.01.00188

https://www.schmalz.com/10.01.01.00188



PFG 40 FPM-65 N007

Part no..:10.01.01.00076

Size: 40
Suction cup material: Fluorocaotchuc FPM
Material hardness [Shore A]: 65 Shore A
Material property: non-marking

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52

schmalz@schmalz.com.mx