Dust filter

STF 40 P 4.5 SSD

Part no..:10.07.01.00398

https://www.schmalz.com/10.07.01.00398


Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Vacuum Filters > Vacuum Filters VF / STF / STF-D > STF 40 P 4.5 SSD

Dust filter



- Connection: Ø40mm
- Shape: Piclon housing
- Nominal flow rate: 270 m³/h
- Filter pore size: 3 µm
- Additional function: Hose clamps SSD

Design Data



Attribute	Value
B1	221 mm
B2	112 mm
d	8.50 mm
D	170 mm
D1	198 mm
D2	40 mm
D3	40 mm
H	218 mm
L	355 mm
L1	658 mm
L2	303 mm
X1	192 mm

Technical Data

Attribute	Value
Connection	Ø40mm
Nominal flow rate	270 m³/h
Nominal flow rate	4500 l/min
Max. vacuum	-500 mbar
Filter pore size	3 µm
Weight	2 kg

Contact Schmalz
Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52
schmalz@schmalz.com.mx

Dust filter

STF 40 P 4.5 SSD

Part no..:10.07.01.00398

https://www.schmalz.com/10.07.01.00398

Product family	VF

Contact Schmalz
Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52
schmalz@schmalz.com.mx