Flat suction cup (round)

SUF 70 NBR-55 G1/4-IG

Part no..:10.01.01.14063

https://www.schmalz.com/10.01.01.14063


Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups SUF > SUF 70 NBR-55 G1/4-IG

Flat suction cup (round) for process safe handling of smooth or slightly rough surfaces



- Size: 70
- Suction cup material: Nitrile rubber NBR
- Material hardness [Shore A]: 55 Shore A
- Vacuum connection: G1/4"-F

Design Data



Attribute	Value
Dmax(S)	77.20 mm
Ds	70 mm
dn	5.10 mm
G1	G1/4"-F
H	34.40 mm
LG1	12 mm
SW1	17 mm
Z (Stroke)	6 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	198 N
Pull-off force	198 N
Volume	18 cm^3
Curve radius (min) (convex)	100 mm
Hose diameter (rec.) d	6 mm
Size	70
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A

Contact Schmalz
Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Flat suction cup (round)

SUF 70 NBR-55 G1/4-IG

Part no..:10.01.01.14063

https://www.schmalz.com/10.01.01.14063

Weight	61.30 g
Product family	SUF
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Contact Schmalz
Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 |
info@schmalz.nl