Flat suction cup (round)

SUF 35 HT1-60 G1/8-AG

Part no..:10.01.01.14106


https://www.schmalz.com/10.01.01.14106

Flat suction cup (round) for process safe handling of smooth or slightly rough surfaces



- Size: 35
- Suction cup material: High temperature material HT1
- Material hardness [Shore A]: 60 Shore A
- Vacuum connection: G1/8"-M

Design Data



Attribute	Value
Dmax(S)	39.20 mm
Ds	35 mm
dn	4.10 mm
G1	G1/8"-M
H	22.10 mm
LG1	7.50 mm
SW1	17 mm
Z (Stroke)	3.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	46 N
Pull-off force	46 N
Volume	2.40 cm³
Curve radius (min) (convex)	40 mm
Hose diameter (rec.) d	4 mm
Size	35
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A

Contact Schmalz
Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Flat suction cup (round)

SUF 35 HT1-60 G1/8-AG


Part no..:10.01.01.14106

https://www.schmalz.com/10.01.01.14106

Weight	14.10 g
Product family	SUF
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SUF 35 HT1-60 SC050

Part no..:10.01.01.13994

Size: 35
Suction cup material: High temperature material HT1
Material hardness [Shore A]: 60 Shore A



SC 050 G1/8-AG

Part no..:10.01.06.04250

Connection geometry: 050
Vacuum connection: G1/8"-M
Fitting length: 7.2 mm
Nominal diameter dn: 4.1 mm