Mono-Base

ISMB-G 80x80x70

Part no..:10.01.15.00156

https://www.schmalz.com/10.01.15.00156


Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Innospann Clamping Equipment ISCUP/ISMB/ISQB > ISMB-G 80x80x70

Mono-Base-G with 2 hose connections for smooth tables



- Dimensions (LxB): 80x80
- Basic area: 80 x 80 mm
- Length L: 80 mm
- Width B: 80 mm
- Height H: 70 mm
- Hose type: Hose D = 8 d = 6

Design Data



Attribute	Value
B	80 mm
d	60 mm
D	6 mm
H	70 mm
L	80 mm

Technical Data

Attribute	Value
Weight	0.42 kg

Accessories

Contact Schmalz
Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Mono-Base

ISMB-G 80x80x70

Part no..:10.01.15.00156

https://www.schmalz.com/10.01.15.00156



ISCUP Cup 1 80x80x30

Part no..:10.01.15.00003

Dimensions (LxB): 80 x 80
Length L: 80 mm
Width B: 80 mm
Height H: 30 mm



ISCUP Cup 2 80x40x30

Part no..:10.01.15.00004

Dimensions (LxB): 80 x 40
Length L: 80 mm
Width B: 40 mm
Height H: 30 mm



ISCUP Cup 3 80x28x30

Part no..:10.01.15.00005

Dimensions (LxB): 80 x 28
Length L: 80 mm
Width B: 28 mm
Height H: 30 mm