Bell suction cup (round)

SAX 60 ED-85 M10-AG

Part no..:10.01.19.00223

https://www.schmalz.com/10.01.19.00223


Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bell-Shaped Suction Cups SAX > SAX 60 ED-85 M10-AG

Bell suction cup (round) for best adaptation to strongly curved surfaces



- Size: 60
- Suction cup material: Elastodur ED
- Material hardness [Shore A]: 85 Shore A
- Connection: M10-M
- Number of folds: 0

Design Data



Attribute	Value
dn	4.10 mm
Dmax(S)	69.70 mm
Ds	61.50 mm
G1	M10-M
H	33.40 mm
LG1	14.50 mm
SW1	22 mm
Z (Stroke)	10.90 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	154 N
Lateral force	107 N
Lateral force (oily surface)	155 N
Volume	25.20 cm^3
Curve radius (min) (convex)	30 mm
Size	60
Connection	M10-M
Number of folds	0

Contact Schmalz
Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Bell suction cup (round)

SAX 60 ED-85 M10-AG

Part no..:10.01.19.00223

https://www.schmalz.com/10.01.19.00223

Suction cup material	Elastodur ED
Material hardness [Shore A]	85 Shore A
Weight	38.50 g
Product family	SAX

Contact Schmalz
Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 |
info@schmalz.nl