Suction area

SAUG-FL SCG 60 POM

Part no..:10.01.30.00031

https://www.schmalz.com/10.01.30.00031


Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Flow Grippers > Suction Cups for Flow Grippers SCG > SAUG-FL SCG 60 POM

Suction plate



External diameter D: 60 mm
Height H: 9.5 mm
Suction cup material: Poloxymethylene POM
Working temperature max.: 80 °C
Construction use: Flow gripper

Design Data



Attribute	Value
D	60 mm
G1	M37x1-F
H	9.50 mm
LG1	6.80 mm

Technical Data

Attribute	Value
Pressure range (operating pressure)	bar
Operating temperature	°C
Weight	16 g
Holding force	4 ... 20 N
Air consumption	m³/h
Air consumption	l/min
Suction rate	m³/h
Suction rate	l/min

Suction area

SAUG-FL SCG 60 POM

Part no..:10.01.30.00031

https://www.schmalz.com/10.01.30.00031

Suction cup material	Poloxymethylene POM
Product family	SAUG-SCG

Accessories



SCG 1xE100 A MA AR M37x1-AG

Part no..:10.01.30.00092

Number of ejectors: 1
Performance class: E100
construction shape compact ejectors: Blow-off function
Add. function: Exhaust air connection axial



SCG 1xE100 A MA SDA M37x1-AG

Part no..:10.01.30.00359

Number of ejectors: 1
Performance class: E100
construction shape compact ejectors: Blow-off function
Add. function: Axial silencer



SCG 1xE100 A MS AR M37x1-AG

Part no..:10.01.30.00170

Number of ejectors: 1
Performance class: E100
construction shape compact ejectors: Blow-off function
Mounting: sideways
Add. function: Exhaust air connection axial

Suction area

SAUG-FL SCG 60 POM

Part no..:10.01.30.00031

https://www.schmalz.com/10.01.30.00031



SCG 1xE100 A MS SDA M37x1-AG

Part no..:10.01.30.00360

Number of ejectors: 1
Performance class: E100
construction shape compact ejectors: Blow-off function
Mounting: sideways
Add. function: Axial silencer