Suction cup (round)


SAUG-SCGS 30 SI-MD-55 602 B

Part no..:10.01.30.01088

https://www.schmalz.com/10.01.30.01088


Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Flow Grippers > Suction Cups for Flow Grippers SCGS > SAUG-SCGS 30 SI-MD-55 602 B

Suction cup (round)



- Size: 30
- Suction cup material: Silicone SI metal detectable
- Material hardness [Shore A]: 55 Shore A
- Suct. cups: Bell. suct. cup f. SCG(S)

Design Data



Attribute	Value
Dmax (N)	25 mm
Dmax(S)	32.50 mm
dn	15 mm
Ds	29.50 mm
G1	M20x1-F
H	26.30 mm
LG1	5 mm
Z (Stroke)	5.50 mm

Technical Data

Attribute	Value
Size	30
Suction cup material	Silicone SI metal detectable
Material hardness [Shore A]	55 Shore A
Weight	10.90 g
Product family	SAUG-SCGS

Contact Schmalz
Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl


Suction cup (round)

SAUG-SCGS 30 SI-MD-55 602 B

Part no..:10.01.30.01088

https://www.schmalz.com/10.01.30.01088

Spare parts



BCG 30 SI-MD-55 SC085

Part no..:10.01.06.04559

Size: 30
Suction cup material: Silicone SI metal detectable
Material hardness [Shore A]: 55 Shore A

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl