# Holder tooling suction Cup


HT-SG A2 I 10 31 G3/8-AG AB VS

Part no..:10.07.06.00542

https://www.schmalz.com/10.07.06.00542


Home > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Holder System for Tooling HT > Holders for Suction Cups HT-SG I > HT-SG A2 I 10 31 G3/8-AG AB VS

## Holder for suction cup



- Connection 1: Bolt with slot Ø19mm
- Shape: integrated nozzle
- Suction cup connection: G3/8"-M
- Vacuum connection: G1/8"-F
- Add. function: Active blowing off

## Design Data




| Attribute | Value |
|---|---|
| B | 31 mm |
| B1 | 80.40 mm |
| B2 | 32 mm |
| D | 19 mm |
| G2 | G3/8"-M |
| G3 | G1/8"-F |
| G4 | G1/8"-F |
| H | 24.50 mm |
| H1 | 59.90 mm |
| L | 39.30 mm |
| L1 | 81.05 mm |
| L2 | 60.80 mm |
| L3 | 11.70 mm |
| LG2 | 22 mm |
| SW1 | 22 mm |

## Technical Data

| Attribute | Value |
|---|---|
| Weight | 231.60 g |
| Product family | HT-SG-I |

Contact Schmalz
Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

# Holder tooling suction Cup

HT-SG A2 I 10 31 G3/8-AG AB VS

Part no..:10.07.06.00542

https://www.schmalz.com/10.07.06.00542

## Accessories



**STV-GE G1/8-AG 6**

Part no..:10.08.02.00204

| |
|---|
| Thread G1: G1/8"-M |
| Hose diameter: 6 mm |
| Material: Brass |
| Operating temperature: -20 ... 80 °C |
| External diameter D: 11.4 mm |
| Length L: 16.4 mm |



**STV-W G1/8-AG 6**

Part no..:10.08.02.00288

| |
|---|
| Thread G1: G1/8"-M |
| Hose diameter: 6 mm |
| Material: Plastics |
| Operating temperature: °C |
| Length L: 20.8 mm |