Flat suction pad (round)

SFF 25 HT1-60 G1/8-AG

Part no..:10.01.01.14278

https://www.schmalz.com/10.01.01.14278


Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > Suction Cups SFF / SFB1 > SFF 25 HT1-60 G1/8-AG

Flat suction cup (round) for dynamic handling of thin and flexible workpieces



- Size: 25
- Suction cup material: High temperature material HT1
- Material hardness [Shore A]: 60 Shore A
- Number of folds: 0

Design Data



Attribute	Value
G1	G1/8"-M
Dmax(S)	26.50 mm
Ds	25 mm
dn	4 mm
LG1	7.50 mm
H	19.20 mm
SW1	14 mm
Z (Stroke)	1.70 mm

Technical Data

Attribute	Value
Size	25
Suction cup material	High temperature material HT1
Suction force (-600mbar)	18.50 N
Product family	SFF
Volume	1.20 cm^3
Number of folds	0
Material hardness [Shore A]	60 Shore A

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0122 | schmalz@schmalz.com.tr


Flat suction pad (round)

SFF 25 HT1-60 G1/8-AG

Part no..:10.01.01.14278

https://www.schmalz.com/10.01.01.14278

Spare parts



SFF 25 HT1-60 SC040

Part no..:10.01.01.14053

Size: 25
Suction cup material: High temperature material HT1
Material hardness [Shore A]: 60 Shore A
Number of folds: 0



SC 040 G1/8-AG

Part no..:10.01.06.02490

Connection geometry: 040
Connection: G1/8"-M
Length L1: 20.2 mm
Fitting length: 6 mm
Nominal diameter dn: 4.1 mm

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 341 0112 | schmalz@schmalz.com.tr