

Bellows suction cups (round)

FSG 5 NBR-55 M5-AG

Číslo dílu...:10.01.06.00663

<https://www.schmalz.com/10.01.06.00663>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups FSG (2.5 Folds) > FSG 5 NBR-55 M5-AG

Bellows suction cup (round) for very uneven workpieces



Size: 5

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A


Nipple material: Aluminum

Connection: M5-M

Number of folds: 2,5

Vacuum connection: M5-M

Údaje o konstrukci



Atribut	Wert
d2	2,60 mm
dn	2 mm
Dmax(S)	7 mm
Ds	5 mm
G1	M5-M
H	19 mm
LG1	5 mm
SW1	8 mm
Z (Stroke)	2 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technické údaje

Atribut	Wert
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Size	5
Number of folds	2,50
Connection	M5-AG
Curve radius (min) (convex)	7,50 mm
Volume	0,03 cm ³

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Bellows suction cups (round)

FSG 5 NBR-55 M5-AG

Číslo dílu...:10.01.06.00663

<https://www.schmalz.com/10.01.06.00663>

Suction force (-600mbar)	0,32 N
Pull-off force	0,80 N
Hose diameter (rec.) d	2 mm
Weight	1,50 g
Product family	FSG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Příslušenství



SPI 6 PEEK

Číslo dílu...:10.01.06.03279

Size: 6

Material: Polyetheretherketon

Náhradní díly



SA-NIP N017 M5-AG DN200

Číslo dílu...:10.01.06.00314

Thread G1: M5-M

Fitting length: 5 mm

Material: Aluminum

Bellows suction cups (round)

FSG 5 NBR-55 M5-AG

Číslo dílu...:10.01.06.00663

<https://www.schmalz.com/10.01.06.00663>



FG 5 NBR-55 N017

Číslo dílu...:10.01.06.00640

Size: 5

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Number of folds: 2,5