

Bellows suction cup SI-HD (round)

FG 7 SI-HD-65 N016

Číslo dílu...:10.01.06.03901

<https://www.schmalz.com/10.01.06.03901>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > FG 7 SI-HD-65 N016

Bellows suction cup (round)for wear-resistant handling



Size: 7


Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A

Material characteristics: FDA-compatible

Number of folds: 2,5

Údaje o konstrukci



Atribut	Wert
d	4,50 mm
d2	1,80 mm
D1	6,50 mm
Dk	9 mm
Dmax(S)	9 mm
Ds	5,90 mm
H	14 mm
H2	3,80 mm
H3	6,50 mm
Z (Stroke)	3 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technické údaje

Atribut	Wert
Suction force (-600mbar)	0,10 N
Pull-off force	0,90 N
Volume	0,16 cm ³
Curve radius (min) (convex)	3 mm
Hose diameter (rec.) d	4 mm
Size	7
Nipple family	N 016

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Bellows suction cup SI-HD (round)

FG 7 SI-HD-65 N016

Číslo dílu...:10.01.06.03901

<https://www.schmalz.com/10.01.06.03901>

Number of folds	2,50
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65 Shore A
Weight	0,50 g
Product family	FG

Příslušenství



SA-NIP N016 G1/8-AG DN350

Číslo dílu...:10.01.06.05735

Nipple family: N 016

Thread G1: G1/8"-M

Length L1: 20 mm

Fitting length: 6 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum



SA-NIP N016 G1/8-IG DN350

Číslo dílu...:10.01.06.05731

Nipple family: N 016

Thread G1: G1/8"-F

Length L1: 18,5 mm

Fitting length: 12 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum

Bellows suction cup SI-HD (round)

FG 7 SI-HD-65 N016

Číslo dílu...:10.01.06.03901

<https://www.schmalz.com/10.01.06.03901>



SA-NIP N016 M5-AG DN250

Číslo dílu...:10.01.06.00123

Nipple family: N 016

Thread G1: M5-M

Length L1: 16 mm

Fitting length: 5 mm

Nominal diameter dn: 2,5 mm

Material: Aluminum



SA-NIP N016 G1/8-AG DN310

Číslo dílu...:10.01.06.04062

Nipple family: N 016

Thread G1: G1/8"-M

Length L1: 20 mm

Fitting length: 6 mm

Nominal diameter dn: 3,1 mm

Spanner size SW2: 3 mm

Material: Aust. Stainless steel



SA-NIP N016 M5-AG DN250

Číslo dílu...:10.01.06.04365

Nipple family: N 016

Thread G1: M5-M

Length L1: 16 mm

Fitting length: 5 mm

Nominal diameter dn: 2,5 mm

Spanner size SW2: 3 mm

Material: Aust. Stainless steel

Bellows suction cup SI-HD (round)

FG 7 SI-HD-65 N016

Číslo dílu...:10.01.06.03901

<https://www.schmalz.com/10.01.06.03901>



SA-NIP N016 M5-IG DN310

Číslo dílu...:10.01.06.04689

Nipple family: N 016

Thread G1: M5-F

Length L1: 16 mm

Fitting length: 10 mm

Nominal diameter dn: 3,1 mm

Spanner size SW2: 3 mm

Material: Aust. Stainless steel



SA-NIP N016 G1/8-IG DN310

Číslo dílu...:10.01.06.04690

Nipple family: N 016

Thread G1: G1/8"-F

Length L1: 18,5 mm

Fitting length: 12 mm

Nominal diameter dn: 3,1 mm

Material: Aust. Stainless steel