

Bellows suction cups SI-HD (round)

FSGA 11 SI-HD-65 M5-AG

Číslo dílu...:10.01.06.04176

<https://www.schmalz.com/10.01.06.04176>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Vacuum Suction Cups > Suction Cups for the Packaging Industry > Bellows Suction Cups FSGA SI-HD (1.5 Folds) > FSGA 11 SI-HD-65 M5-AG

Bellows suction cup (round) with optimal adaptation to uneven surfaces



Size: 11

Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A

Material characteristics: FDA-compatible


Nipple material: Aluminum

Connection: M5-M

Number of folds: 1,5

Vacuum connection: M5-M

Údaje o konstrukci



Atribut	Wert
d2	5,10 mm
Dmax(S)	13 mm
dn	2,50 mm
Ds	10,40 mm
G1	M5-M
H	21 mm
LG1	5 mm
SW1	7 mm
Z (Stroke)	4 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technické údaje

Atribut	Wert
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65 Shore A
Size	11
Number of folds	1,50
Connection	M5-AG
Curve radius (min) (convex)	10 mm
Volume	0,23 cm ³

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Bellows suction cups SI-HD (round)

FSGA 11 SI-HD-65 M5-AG

Číslo dílu...:10.01.06.04176

<https://www.schmalz.com/10.01.06.04176>

Suction force (-600mbar)	0,95 N
Pull-off force	3,80 N
Hose diameter (rec.) d	2 mm
Weight	2 g
Product family	FSGA

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Příslušenství



SPI 11 PEEK

Číslo dílu...:10.01.06.03281

Size: 11

Material: Polyetheretherketon

Náhradní díly



SA-NIP N016 M5-AG DN250

Číslo dílu...:10.01.06.00123

Nipple family: N 016

Thread G1: M5-M

Length L1: 16 mm

Fitting length: 5 mm

Nominal diameter dn: 2,5 mm

Material: Aluminum

Bellows suction cups SI-HD (round)

FSGA 11 SI-HD-65 M5-AG

Číslo dílu...:10.01.06.04176

<https://www.schmalz.com/10.01.06.04176>



FGA 11 SI-HD-65 N016

Číslo dílu...:10.01.06.03986

Size: 11

Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A

Material characteristics: FDA-compatible

Number of folds: 1,5