

Bellows suction cup (round)

SPB1 80 ED-65 SC065

Číslo dílu...:10.01.06.03071

<https://www.schmalz.com/10.01.06.03071>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Vacuum Suction Cups > Suction Cups for the Packaging Industry > SPB1 80 ED-65 SC065

Bellows suction cup (round) with 1.5 corr. for dynamic handling of cardboard and rigid packaging




Size: 80

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Number of folds: 1,5

Údaje o konstrukci



Atribut	Wert
d	14 mm
d1	29,30 mm
d2	56 mm
D1	82,70 mm
Dk	27,10 mm
Dmax(S)	88 mm
Ds	81,40 mm
H	45,90 mm
H2	15,30 mm
Z (Stroke)	23,50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technické údaje

Atribut	Wert
Suction force (-600mbar)	166 N
Pull-off force	200 N
Lateral force	59 N
Volume	98,36 cm ³
Curve radius (min) (convex)	70 mm
Hose diameter (rec.) d	6 mm
Size	80

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Bellows suction cup (round)

SPB1 80 ED-65 SC065

Číslo dílu...:10.01.06.03071

<https://www.schmalz.com/10.01.06.03071>

Nipple family	SC 065
Number of folds	1,50
Suction cup material	Elastodur ED
Material hardness [Shore A]	65 Shore A
Weight	40,10 g
Product family	SPB1

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Příslušenství



SC 065 G1/4-AG L MOD

Číslo dílu...:10.01.06.03193

Connection geometry: 065

Connection: G1/4"-M

Length L1: 36,1 mm

Fitting length: 8 mm

Nominal diameter dn: 6,1 mm

Shape: Self Locking



SC 065 G1/4-IG L MOD

Číslo dílu...:10.01.06.03194

Connection geometry: 065

Connection: G1/4"-F

Length L1: 36,1 mm

Fitting length: 18 mm

Nominal diameter dn: 6,1 mm

Shape: Self Locking

Bellows suction cup (round)

SPB1 80 ED-65 SC065

Číslo dílu...:10.01.06.03071

<https://www.schmalz.com/10.01.06.03071>



SIEB 32.5x0.8 MS-A2 280 0.28/0.16

Číslo dílu...:10.07.01.00364

External diameter D: 32,5 mm

Length L: 0,8 mm

Material: Brass / Stainless steel

Filter pore size: 280 µm