

Bell suction cup (round)

SAXM 115 ED-85 SC065

Part no...:10.01.19.00010

<https://www.schmalz.com/10.01.19.00010>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > SAXM 115 ED-85 SC065

High-Speed bell shaped suction cup (round) very dynamic handling of smooth and oily workpieces




Size: 115

Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Design Data



Attribute	Value
d	14 mm
d1	39.60 mm
Dk	28.90 mm
Dmax(S)	129.40 mm
Ds	115.20 mm
H	42.30 mm
H2	14.30 mm
Z (Stroke)	20 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	549 N
Lateral force	320 N
Lateral force (oily surface)	584 N
Volume	150.05 cm ³
Curve radius (min) (convex)	50 mm
Hose diameter (rec.) d	6 mm
Size	115

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Bell suction cup (round)

SAXM 115 ED-85 SC065

Part no...:10.01.19.00010

<https://www.schmalz.com/10.01.19.00010>

Nipple family	SC 065
Number of folds	0
Suction cup material	Elastodur ED
Material hardness [Shore A]	85 Shore A
Weight	52.70 g
Product family	SAXM

Accessories



SC-A 065 G1/4-AG L

Part no...:10.01.06.02824

Connection geometry: 065

Thread G1: G1/4"-M

Fitting length: 8 mm

Shape: Self Locking



SC-A 065 G1/4-IG L

Part no...:10.01.06.02774

Connection geometry: 065

Thread G1: G1/4"-F

Fitting length: 18 mm

Shape: Self Locking

Bell suction cup (round)

SAXM 115 ED-85 SC065

Part no...:10.01.19.00010

<https://www.schmalz.com/10.01.19.00010>



SC-A 065 G3/8-AG L

Part no...:10.01.06.02810

Connection geometry: 065

Thread G1: G3/8"-M

Fitting length: 8 mm

Shape: Self Locking



SC-A 065 G3/8-IG L

Part no...:10.01.06.02648

Connection geometry: 065

Thread G1: G3/8"-F

Fitting length: 18 mm

Shape: Self Locking



SC-A 065 M10-AG L

Part no...:10.01.06.02825

Connection geometry: 065

Thread G1: M10-M

Fitting length: 8 mm

Shape: Self Locking

Bell suction cup (round)

SAXM 115 ED-85 SC065

Part no...:10.01.19.00010

<https://www.schmalz.com/10.01.19.00010>



SC-A 065 M14x1.5-AG L

Part no...:10.01.06.02826

Connection geometry: 065

Thread G1: M14x1.5-M

Fitting length: 8 mm

Shape: Self Locking



SC-A 065 RA L

Part no...:10.01.06.02817

Connection geometry: 065

Fitting length: 9.5 mm

Shape: Self Locking



SC-S 065 FDC-L

Part no...:10.01.06.02805

Shape: Frict elem with Self lock