

Suction Cup Balance SSCB

SSCB-78 141-171 ZP M6-IG FSG-VU1

Part no.:10.01.15.00922

<https://www.schmalz.com/10.01.15.00922>

Home > Vacuum Clamping Technology > Clamping Equipment for 3D Freeform Surfaces > Clamping and Gripping Equipment for Automated Processing > Suction Cup Balance SSCB > SSCB-78 141-171 ZP M6-IG FSG-VU1

Vacuum Clamping System for automated 3D-fixation



Pitch diameter D mk: 78 mm

Function Suction cup: Centrally fixed pins

Suct. cups: Bellows suct. cup FSG

Connection: M6-F


Material: VU1

Material hardness [Shore A]: 72 Shore A

Material: NBR

Height H1: 179 mm

Design Data



Attribute	Value
D1	134 mm
Dmk	78 mm
D mk1	48 mm
G1	M6-F
G2	G1/4"-F
H1	179 mm
EH (min)	141 mm
EH (max)	171 mm
Zs	30 mm
Z (Stroke)	46 mm

Technical Data

Attribute	Value
Size	60
Weight	2,609.70 g
Suction cup material	Vulkollan VU1
Material hardness [Shore A]	72 Shore A

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au

Suction Cup Balance SSCB

SSCB-78 141-171 ZP M6-IG FSG-VU1

Part no.:10.01.15.00922

<https://www.schmalz.com/10.01.15.00922>

Accessories



ERS SSCB-FG60-VU1

Part no.:10.01.15.00953

Construction use: Suction-Cup Balance

Size: FG60-VU1

Spare parts



ERS SSCB-FG60-VU1

Part no.:10.01.15.00953

Construction use: Suction-Cup Balance

Size: FG60-VU1



KAPP 7x10.5 SSCB

Part no.:10.01.15.00918

External diameter D: 7 mm

Length L: 10.5 mm

Construction use: Suction-Cup Balance

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au



Suction Cup Balance SSCB

SSCB-78 141-171 ZP M6-IG FSG-VU1

Part no...:10.01.15.00922

<https://www.schmalz.com/10.01.15.00922>

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au