

## Flat suction cup (round)

SFF 40 HT1-60 SC050

Part no.: 10.01.01.14055

<https://www.schmalz.com/10.01.01.14055>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > SFF 40 HT1-60 SC050

### Flat suction cups (round) for the gentle handling of thin and flexible workpieces




Size: 40

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Number of folds: 0

### Design Data



| Attribute  | Value    |
|------------|----------|
| Dmax(S)    | 42 mm    |
| Dk         | 21.90 mm |
| Ds         | 40 mm    |
| d          | 11.40 mm |
| d1         | 17.10 mm |
| H          | 19 mm    |
| H2         | 6.60 mm  |
| H3         | 9.50 mm  |
| Z (Stroke) | 2.70 mm  |

### Technical Data

| Attribute                   | Value                         |
|-----------------------------|-------------------------------|
| Suction force (-600mbar)    | 48.60 N                       |
| Volume                      | 4.33 cm <sup>3</sup>          |
| Size                        | 40                            |
| Number of folds             | 0                             |
| Suction cup material        | High temperature material HT1 |
| Material hardness [Shore A] | 60 Shore A                    |
| Curve radius (min) (convex) | 45 mm                         |
| Nipple family               | SC 050                        |

### Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | [schmalz@schmalz.at](mailto:schmalz@schmalz.at)

## Flat suction cup (round)

SFF 40 HT1-60 SC050

Part no.:10.01.01.14055

<https://www.schmalz.com/10.01.01.14055>

|                |        |
|----------------|--------|
| Weight         | 6.70 g |
| Product family | SFF    |

### Accessories



#### SC 050 G1/4-AG SW410

Part no.:10.01.06.04347

Connection geometry: 050

Vacuum connection: G1/4"-M

Fitting length: 7.2 mm

Nominal diameter dn: 4.1 mm



#### SC 050 G1/4-IG SW410

Part no.:10.01.06.04348

Connection geometry: 050

Vacuum connection: G1/4"-F

Fitting length: 17.2 mm

Nominal diameter dn: 4.1 mm

### Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | [schmalz@schmalz.at](mailto:schmalz@schmalz.at)