

## Plug union, elbow

STV-W M5-AG 6

Part no.:10.08.02.00296

<https://www.schmalz.com/10.08.02.00296>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STV-W M5-AG 6

### Push-in Fitting, swivelling elbow




Pressure range (operating pressure): bar

Length L: 20.8 mm

Height H: 13 mm

Thread G1: M5-M

### Design Data



| Attribute | Value    |
|-----------|----------|
| d         | 6 mm     |
| D1        | 11.50 mm |
| dn        | 4 mm     |
| G1        | M5-M     |
| H         | 13 mm    |
| H1        | 16.50 mm |
| L         | 20.80 mm |
| L1        | 25.50 mm |
| LG1       | 4 mm     |
| SW1       | 8 mm     |
| SW3       | 8 mm     |

### Technical Data

| Attribute | Value  |
|-----------|--------|
| Weight    | 4.30 g |

### Accessories

#### Contact Schmalz


Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | [schmalz@schmalz.ca](mailto:schmalz@schmalz.ca)

## Plug union, elbow

STV-W M5-AG 6

Part no.:10.08.02.00296

<https://www.schmalz.com/10.08.02.00296>



### VSL 6-4 PE BL

Part no.:10.07.09.00014

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



### VSL 6-4 PTFE MI-TR

Part no.:10.07.09.00157

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 50 m

Material hose: Polytetrafluorethylene

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -190 ... 260 °C



### VSL 6-4 PU MI-TR

Part no.:10.07.09.00002

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C

## Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | [schmalz@schmalz.ca](mailto:schmalz@schmalz.ca)