

Vacuum block

VCBL-S6 145x145x50 TV+ME

Part no.:10.01.12.04460

<https://www.schmalz.com/10.01.12.04460>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Systems from SCM / Morbidelli > Vacuum Blocks VCBL-S6 > VCBL-S6 145x145x50 TV+ME

Vacuum block for SCM/Morbidelli console - Type 6




Dimensions (LxB): 145x145

Height H: 50 mm

Add. function: Sensing valve + diaphragm

Application: For machine tables Flexmatic, Start and Pilot further accessories are required

Design Data



Attribute	Value
B	145 mm
H	50 mm
H1	87.50 mm
L	145 mm
L2	104 mm

Technical Data

Attribute	Value
Application	For machine tables Flexmatic, Start and Pilot further accessories are required

Accessories

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca

Vacuum block

VCBL-S6 145x145x50 TV+ME

Part no...:10.01.12.04460

<https://www.schmalz.com/10.01.12.04460>



VCSP-O 145x145x17.9 ME-MOS TPE

Part no...:10.01.12.04818

Construction use: VCBL-S6

Length L: 145 mm

Width B: 145 mm

Height H: 17.9 mm



SCHA-NOCK 12x7.6x20 VCBL-S6

Part no...:10.01.12.04741

Length L: 12 mm

Width B: 7.6 mm

Height H: 20 mm

Construction use: VCBL-S6

Application: For Flexmatic machine tables with automatic positioning



ZUB VCBL-S6

Part no...:10.01.12.04841

Construction use: VCBL-S6

Application: for start and pilot machine tables with position detection

Spare parts

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca

Vacuum block

VCBL-S6 145x145x50 TV+ME

Part no...:10.01.12.04460

<https://www.schmalz.com/10.01.12.04460>



VCSP-O 145x145x16.5 ME TPE

Part no...:10.01.12.04445


Construction use: Vacuum block

Length L: 145 mm

Width B: 145 mm

Height H: 16.5 mm

Add. function: Membrane



VCDR 135x25.5x6 VCBL

Part no...:10.01.12.04560

Length L: 135 mm

Width B: 25.5 mm

Height H: 6 mm

Construction use: Vacuum block



TV D9 4.3

Part no...:10.01.12.02514

External diameter D: 9 mm

Spring stroke Z: 4.3 mm

Length L: 22.8 mm