Vacuum pump

EVE-OG 10 AC3

Part no..:10.03.02.00067

https://www.schmalz.com/10.03.02.00067


Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Pumps > Oil-Lubricated Vacuum Pumps EVE-OG > EVE-OG 10 AC3

Oil-lubricated pump for maximum vacuum levels, requires little maintenance



- Current type: three-phase current
- Sound level at 50 Hz: 49 dB(A)
- Suction rate (50 Hz): 10 m³/h
- Rated power 50 Hz: 0.37 kW
- Voltage at 50Hz: 230/400V AC
- Weight: 19 kg

Design Data



Attribute	Value
B	212 mm
B2	26 mm
G3	G3/4"-F
G5	M8-F
H	211 mm
L	422 mm
L2	63 mm
X1	176 mm
Y1	111 mm

Technical Data

Attribute	Value
Max. vacuum	-980 mbar
Max. vacuum	-28.94 inHg
Suction rate (50 Hz)	10 m³/h
Voltage at 50Hz	230/400V AC
Rated power 50 Hz	0.37 kW
Sound level at 50 Hz	49 dB(A)
Weight	19 kg
Protection type IP	IP 54

Vacuum pump

EVE-OG 10 AC3

Part no..:10.03.02.00067

https://www.schmalz.com/10.03.02.00067

Current type	AC3
Product family	EVE-OG

Accessories



DRM 40 P1 H

Part no..:10.07.02.00050

External diameter D: 40 mm
Measuring range: 0,0 ... 1,0 bar
Construction shape manometers: Connection at rear
Thread G1: G3/4"-M



MSS-K 1-1.6A

Part no..:10.04.04.00118

Construction use: PKZM0
Protection type IP: IP 65
Measuring range: bar



VOL 15

Part no..:10.03.03.00113

Reservoirs volume: 15 l
Height H: 180 mm
Add. function: Manometer, valve, filter

Vacuum pump

EVE-OG 10 AC3

Part no..:10.03.02.00067

https://www.schmalz.com/10.03.02.00067



OEL EVE-OG 1L ANDEROL 555

Part no..:27.02.01.00055

Construction use: Pump EVE-OG



ZUB EVE-OG Ölablass-Kit

Part no..:22.09.03.00038

Construction use: Pump EVE-OG

Spare parts



FILT-EINS 3 65x70 PAP STF-3/4-IG

Part no..:10.07.01.00017

Filter pore size: 3 µm

External diameter D: 65 mm

Length L: 69.5 mm

Filter material: Paper

Construction use: Dust filter STF

Size: 3/4-IG

Vacuum pump

EVE-OG 10 AC3

Part no..:10.03.02.00067

https://www.schmalz.com/10.03.02.00067



OEL EVE-OG 1L ANDEROL 555

Part no..:27.02.01.00055

Construction use: Pump EVE-OG



VST EVE-OG-10-16C

Part no..:10.03.02.00075

Construction use: Pump EVE-OG

Size: 10-16C