

Vacuum pump

EVE-OG 25 AC3

Part no.:10.03.02.00084

<https://www.schmalz.com/10.03.02.00084>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Pumps > Oil-Lubricated Vacuum Pumps EVE-OG > EVE-OG 25 AC3

Oil-lubricated pump for maximum vacuum levels, requires little maintenance



Suction rate (60 Hz): 30 m³/h

Current type: three-phase current

Sound level at 50 Hz: 60 dB(A)

Suction rate (50 Hz): 25 m³/h


Rated power 50 Hz: 0.75 kW

Voltage at 50Hz: 230/400V AC

Voltage at 60Hz: 230/400V - AC

Weight: 34 kg

Design Data



Attribute	Value
B	284 mm
B2	17 mm
G3	G1-1/4"-F
G5	M8-F
H	260 mm
L	568 mm
L2	131 mm
X1	159 mm
X2	120 mm
Y1	238 mm
Y2	171 mm

Technical Data

Attribute	Value
Max. vacuum	-980 mbar
Max. vacuum	-28.94 inHg
Suction rate (50 Hz)	25 m ³ /h
Voltage at 50Hz	230/400V AC
Rated power 50 Hz	0.75 kW
Sound level at 50 Hz	60 dB(A)

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca

Vacuum pump

EVE-OG 25 AC3

Part no.:10.03.02.00084

<https://www.schmalz.com/10.03.02.00084>

Weight	34 kg
Protection type IP	IP 54
Current type	AC3
Product family	EVE-OG

Accessories



DRM 40 P1 H

Part no.:10.07.02.00050

External diameter D: 40 mm

Measuring range: 0,0 ... 1,0 bar

Construction shape manometers: Connection at rear

Thread G1: G3/4"-M



MSS-K 2.5-4A

Part no.:10.04.04.00120

Construction use: PKZM0

Protection type IP: IP 65

Measuring range: bar

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca

Vacuum pump

EVE-OG 25 AC3

Part no...:10.03.02.00084

<https://www.schmalz.com/10.03.02.00084>



VST EVE-OG-10-16C

Part no...:10.03.02.00075

Construction use: Pump EVE-OG

Size: 10-16C



VOL 50

Part no...:10.03.03.00118

Reservoirs volume: 50 l

Height H: 235 mm

Add. function: Manometer, valve, filter



ZUB EVE-OG Ölabblass-Kit

Part no...:22.09.03.00038

Construction use: Pump EVE-OG

Spare parts

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca

Vacuum pump

EVE-OG 25 AC3

Part no...:10.03.02.00084

<https://www.schmalz.com/10.03.02.00084>



FILT-EINS 3 65x70 PAP STF-3/4-IG

Part no...:10.07.01.00017

Filter pore size: 3 µm

External diameter D: 65 mm

Length L: 69.5 mm

Filter material: Paper

Construction use: Dust filter STF

Size: 3/4-IG



OEL EVE-OG 1L ANDEROL 555

Part no...:27.02.01.00055

Construction use: Pump EVE-OG



VST EVE-OG-10-16C

Part no...:10.03.02.00075

Construction use: Pump EVE-OG

Size: 10-16C

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca

Vacuum pump

EVE-OG 25 AC3

Part no...:10.03.02.00084

<https://www.schmalz.com/10.03.02.00084>



VST EVE-OG-25-40

Part no...:10.03.02.00060

Construction use: Pump EVE-OG

Size: 25-40

Contact Schmalz

Schmalz Vacuum Technology Ltd. | 14-2900 Argentia Rd, L5N 7X9 Mississauga, ON, Canada | +1 905 569 9520 | schmalz@schmalz.ca