

angle piece (geared)

SXT-ANG-GB2-M

Part no.:10.07.13.00120

<https://www.schmalz.com/10.07.13.00120>

Home > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Tooling System SXT > Elbow Connectors (Geared) SXT-ANG > SXT-ANG-GB2-M

Angle gear piece, modular, for swivel arms and to connect with Round Tooling




Material: Aluminum

Shape: Male

Shape: Gear Bracket both sides

Design Data



Attribute	Value
D	35 mm
d	8.50 mm
H	42.50 mm
H2	25 mm
L	42.50 mm
L2	25 mm

Technical Data

Attribute	Value
Material	Aluminum
Weight	80 g
Shape	Male
Product family	SXT

Contact Schmalz

Schmalz GmbH | Eigentlstr. 1, 8309 Nürensdorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch

angle piece (geared)

SXT-ANG-GB2-M

Part no.:10.07.13.00120

<https://www.schmalz.com/10.07.13.00120>

Accessories



SXT-CON-GB-F-D25

Part no.:10.07.13.00114

Material: Aluminum

Connection 1: D25

Shape: Female



SXT-CON-GB-F-D40

Part no.:10.07.13.00115

Material: Aluminum

Connection 1: D40

Shape: Female



SXT-CON-GB-F-1IN

Part no.:10.07.13.00191

Material: Aluminum

Connection 1: 1 Inch

Shape: Female

angle piece (geared)

SXT-ANG-GB2-M

Part no...:10.07.13.00120

<https://www.schmalz.com/10.07.13.00120>



SXT-EXT-GB2-50

Part no...:10.07.13.00034

External diameter D: 25 mm

Length L: 50.8 mm

Material: Aluminum

Shape: Gear Braket both sides



SET SCHRAUBE FED-SCHE M8x25

Part no...:10.07.13.00172

Thread G: M8

Length L: 25 mm



SET SCHRAUBE FED-SCHE M8x50

Part no...:10.07.13.00175

Thread G: M8

Length L: 50 mm

angle piece (geared)

SXT-ANG-GB2-M

Part no...:10.07.13.00120

<https://www.schmalz.com/10.07.13.00120>



SET SCHRAUBE FED-SCHE M8x55

Part no...:10.07.13.00176

Thread G: M8

Length L: 55 mm



SET SCHRAUBE FED-SCHE M8x60

Part no...:10.07.13.00177

Thread G: M8

Length L: 60 mm



SET SCHRAUBE FED-SCHE M8x65

Part no...:10.07.13.00178

Thread G: M8

Length L: 65 mm