

Vacuum pump

EVE-TR 100 AC3 IE3-TYP3

Part no.: 10.03.01.00385

<https://www.schmalz.com/10.03.01.00385>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Pumps > Dry-Running Vacuum Pumps EVE-TR > EVE-TR 100 AC3 IE3-TYP3

Oil-free pump with constant suction rate, robust, requires little maintenance



Current type: three-phase current

Sound level at 50 Hz: 75 dB(A)

Voltage at 50Hz: D200/Y350V $\pm 10\%$ (o. IE3)

Voltage at 60Hz: D220V/Y380-400V $\pm 10\%$

Suction rate (50 Hz): 98 m³/h

Suction rate (60 Hz): 112 m³/h

Vacuum (50 Hz): -900 mbar

Rated power 50 Hz: 3 kW


Rated power 60 Hz: 3.6 kW

Construction: IE3:JPN/KOR/BRA

Permission: UL/CSA

Weight: 108 kg

Design Data



Attribute	Value
B	470 mm
B2	107.50 mm
d	12 mm
G3	G1-1/2"-F
G5	M8-F
H	336 mm
L	851 mm
L2	140 mm
X1	398 mm
Y1	245 mm
Y2	122.50 mm

Technical Data

Attribute	Value
Suction rate (50 Hz)	98 m ³ /h
Suction rate (60 Hz)	112 m ³ /h
Voltage at 50Hz	D200/Y350V $\pm 10\%$ (o. IE3)
Voltage at 60Hz	D220V/Y380-400V $\pm 10\%$
Rated power 50 Hz	3 kW

Contact Schmalz

Schmalz GmbH | Eigentlstr. 1, 8309 Nürensdorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch

Vacuum pump

EVE-TR 100 AC3 IE3-TYP3

Part no.:10.03.01.00385

<https://www.schmalz.com/10.03.01.00385>

Rated power 60 Hz	3.60 kW
Current type	AC3
Current type	three-phase current
Construction	IE3:JPN/KOR/BRA
Sound level at 50 Hz	75 dB(A)
Weight	108 kg
Protection type IP	IP 55
Product family	EVE-TR

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

Accessories



VBV -950...0 G1-1/4-AG EVE 60-140

Part no.:10.03.01.00153

External diameter D: 58 mm

Max. vacuum: -950 mbar

Thread G1: G1-1/4"-M

Length L: 72 mm

Construction use: Pump EVE

Size: 60-140



ZUB EVE-TR 10-140, Presse mit Fett

Part no.:10.03.01.00540

Construction use: Pump EVE-TR

Contact Schmalz

Schmalz GmbH | Eigentelstr. 1, 8309 Nürens Dorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch

Vacuum pump

EVE-TR 100 AC3 IE3-TYP3

Part no...:10.03.01.00385

<https://www.schmalz.com/10.03.01.00385>



VOL 100

Part no...:10.03.03.00123

Reservoirs volume: 100 l

Height H: 334 mm

Add. function: Manometer, valve, filter

Spare parts



FILT-EINS 3 98x70 PAP STF-1-1/4-IGN

Part no...:10.07.01.00018

Filter pore size: 3 µm

External diameter D: 98 mm

Length L: 70 mm

Filter material: Paper

Construction use: Dust filter STF

Size: 1-1/4-IGN



VST EVE-TR-100

Part no...:22.09.01.00033

Construction use: Pump EVE-TR

Size: 100

Contact Schmalz

Schmalz GmbH | Eigentelstr. 1, 8309 Nürens Dorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch