

Flat suction cup (round)

SGP 24 SI-50 N016

Part no.:10.01.01.10577

<https://www.schmalz.com/10.01.01.10577>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > SGP 24 SI-50 N016

Flat suction cup (round) for careful gripping of paper, plastic film, etc.




Size: 24

Suction cup material: Silicone SI

Material hardness [Shore A]: 50 Shore A

Design Data



Attribute	Value
d	4.50 mm
Dk	10.50 mm
Dmax(S)	25.50 mm
Ds	24 mm
H	10.80 mm
H2	7.30 mm
Z (Stroke)	1.70 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	11 N
Volume	0.85 cm ³
Size	24
Nipple family	N 016
Number of folds	0
Suction cup material	Silicone SI
Material hardness [Shore A]	50 Shore A

Contact Schmalz

Schmalz GmbH | Eigentlstr. 1, 8309 Nürensdorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch

Flat suction cup (round)

SGP 24 SI-50 N016

Part no.:10.01.01.10577

<https://www.schmalz.com/10.01.01.10577>

Weight

1.10 g

Product family

SGP

Accessories



SA-NIP N016 G1/8-AG DN350

Part no.:10.01.06.05735

Nipple family: N 016

Thread G1: G1/8"-M

Length L1: 20 mm

Fitting length: 6 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum



SA-NIP N016 G1/8-IG DN350

Part no.:10.01.06.05731

Nipple family: N 016

Thread G1: G1/8"-F

Length L1: 18.5 mm

Fitting length: 12 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum



SA-NIP N016 M5-AG DN250

Part no.:10.01.06.00123

Nipple family: N 016

Thread G1: M5-M

Length L1: 16 mm

Fitting length: 5 mm

Nominal diameter dn: 2.5 mm

Material: Aluminum

Contact Schmalz

Schmalz GmbH | Eigentlstr. 1, 8309 Nürens Dorf, Switzerland | +41 44 555 05 05 | schmalz@schmalz.ch

Flat suction cup (round)

SGP 24 SI-50 N016

Part no...:10.01.01.10577

<https://www.schmalz.com/10.01.01.10577>
