

Vacuum block

VCBL-B 140x130x29 TV

Part no.:10.01.12.03165

<https://www.schmalz.com/10.01.12.03165>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Systems from Biesse > Vacuum Blocks
VCBL-B > VCBL-B 140x130x29 TV

Vacuum block




Dimensions (LxB): 140 x 130

Height H: 29 mm

Add. function: Sensing valve

Design Data



Attribute	Value
B	129 mm
H	29 mm
H2	26 mm
L	140 mm
L1	146 mm
L2	6 mm

Technical Data

Attribute	Value
Weight	0.43 kg

Biesse is a registered and protected trademark. The articles listed here are products of J. Schmalz GmbH that have been designed to fit CNC machining centers from Biesse.

Accessories

Contact Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Vacuum block

VCBL-B 140x130x29 TV

Part no...:10.01.12.03165

<https://www.schmalz.com/10.01.12.03165>



SCHE 90/17x0.4 ST VCBL-B

Part no...:10.01.12.03188

External diameter D: 90 mm

Internal diameter d: 17 mm

Height H: 0.4 mm

Length L: 0.4 mm

Material: Steel

Construction use: Vacuum block VCBL-S



VCSP-O 140x130x18.3 MOS TPE

Part no...:10.01.12.03506

Construction use: Vacuum block

Length L: 140 mm

Width B: 130 mm

Height H: 18.3 mm

Add. function: Sealing lip with MOS

Spare parts



ADP-RING-100.5x15.5-VCBL-B

Part no...:10.01.12.03345

External diameter D: 100.5 mm

Height H: 15.5 mm

Construction use: Vacuum block VCBL-S

Contact Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Vacuum block

VCBL-B 140x130x29 TV

Part no...:10.01.12.03165

<https://www.schmalz.com/10.01.12.03165>



VCSP-O 140x130x16.5 TPE

Part no...:10.01.12.02325

Construction use: Vacuum block

Length L: 140 mm

Width B: 130 mm

Height H: 16.5 mm



ERS VCTV

Part no...:10.01.12.01651

Construction use: Sensing valve vacuum block



TV D9 4.3

Part no...:10.01.12.02514

External diameter D: 9 mm

Spring stroke Z: 4.3 mm

Length L: 22.8 mm