

Vacuum block

VCBL-S1 140x115x32.7 D-360 TV

Part no...:10.01.12.01299

<https://www.schmalz.com/10.01.12.01299>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Systems from SCM / Morbidelli > Vacuum Blocks VCBL-S1 > VCBL-S1 140x115x32.7 D-360 TV

Vacuum block for SCM/Morbidelli console - Type 1



Dimensions (LxB): 140 x 115

Length L: 140 mm


Width B: 115 mm

Height H: 32.7 mm

Arrangement: Can be turned 360°

Add. function: Sensing valve

Design Data



Attribute	Value
B	115 mm
B1	120 mm
L	140 mm
H	32.70 mm

Technical Data

Attribute	Value
Weight	0.62 kg

Spare parts

Contact Schmalz


Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Vacuum block

VCBL-S1 140x115x32.7 D-360 TV

Part no...:10.01.12.01299

<https://www.schmalz.com/10.01.12.01299>



VST VCBL-S DI-RA

Part no...:10.01.12.03573

Construction use: Vacuum block VCBL-S

Clamping range: mm



TV D9 4.3

Part no...:10.01.12.02514

External diameter D: 9 mm

Spring stroke Z: 4.3 mm

Length L: 22.8 mm



VCSP-U 140x115x16.5 VCBL-K1 TPE

Part no...:10.01.12.00228

Length L: 140 mm

Width B: 115 mm

Height H: 16.5 mm

Contact Schmalz


Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Vacuum block

VCBL-S1 140x115x32.7 D-360 TV

Part no...:10.01.12.01299

<https://www.schmalz.com/10.01.12.01299>



VCDR 115.5x43x5 VCBL-S

Part no...:10.01.12.03569

Length L: 115.5 mm

Width B: 43 mm

Height H: 5 mm

Construction use: Vacuum block VCBL-S

Clamping range: mm



TV D9 4.3

Part no...:10.01.12.02514

External diameter D: 9 mm

Spring stroke Z: 4.3 mm

Length L: 22.8 mm

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es