

## Vacuum block

VCBL-S4 125x75x50 D-360 TV

Part no...:10.01.12.01473

<https://www.schmalz.com/10.01.12.01473>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Systems from SCM / Morbidelli > Vacuum Blocks VCBL-S4 > VCBL-S4 125x75x50 D-360 TV

### Vacuum block for SCM/Morbidelli console - Type 4



Dimensions (LxB): 125 x 75

Length L: 125 mm


Width B: 75 mm

Height H: 50 mm

Arrangement: Can be turned 360°

Add. function: Sensing valve

### Design Data



| Attribute | Value  |
|-----------|--------|
| B         | 75 mm  |
| B1        | 145 mm |
| H         | 50 mm  |
| H2        | 34 mm  |
| L         | 125 mm |
| L1        | 145 mm |
| L2        | 109 mm |
| R1        | 223 mm |

### Technical Data

| Attribute | Value   |
|-----------|---------|
| Weight    | 0.80 kg |

### Accessories

#### Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | [schmalz@schmalz.es](mailto:schmalz@schmalz.es)

## Vacuum block

VCBL-S4 125x75x50 D-360 TV

Part no...:10.01.12.01473

<https://www.schmalz.com/10.01.12.01473>



**VCSP-O 125x75x17.7 MOS TPE**

Part no...:10.01.12.03511

Construction use: Vacuum block

Length L: 125 mm

Width B: 75 mm

Height H: 17.7 mm

Add. function: Sealing lip with MOS

## Spare parts



**VCSP-O 140x130x16.5 TPE**

Part no...:10.01.12.02325

Construction use: Vacuum block

Length L: 140 mm

Width B: 130 mm

Height H: 16.5 mm



**TV D9 4.3**

Part no...:10.01.12.02514

External diameter D: 9 mm

Spring stroke Z: 4.3 mm

Length L: 22.8 mm

## Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | [schmalz@schmalz.es](mailto:schmalz@schmalz.es)

## Vacuum block

VCBL-S4 125x75x50 D-360 TV

Part no...:10.01.12.01473

<https://www.schmalz.com/10.01.12.01473>



### VCSP-O 125x75x16.5 TPE

Part no...:10.01.12.00011

Length L: 125 mm

Width B: 75 mm

Height H: 16.5 mm



### TV D9 4.3

Part no...:10.01.12.02514

External diameter D: 9 mm

Spring stroke Z: 4.3 mm

Length L: 22.8 mm



### VCDR 141x77.4x3 VCBL-S

Part no...:10.01.14.00235

Length L: 141 mm

Width B: 77.4 mm

Height H: 3 mm

Construction use: Vacuum block VCBL-S

Clamping range: mm

## Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | [schmalz@schmalz.es](mailto:schmalz@schmalz.es)