

Vacuum pump

EVE-OG 25 AC3 F

Part no.:10.03.02.00020

<https://www.schmalz.com/10.03.02.00020>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Pumps > Oil-Lubricated Vacuum Pumps EVE-OG > EVE-OG 25 AC3 F

Oil-lubricated pump for maximum vacuum levels, requires little maintenance



Current type: three-phase current


with: Filter

Suction rate (50 Hz): 25 m³/h

Rated power 50 Hz: 0.75 kW

Weight: 34.5 kg

Design Data



Attribute	Value
B	284 mm
B2	17 mm
G2	G3/4"-F
G3	G1-1/4"-F
G5	M8-F
H	260 mm
H1	380 mm
H2	75 mm
L	568 mm
L2	131 mm
X1	159 mm
X2	120 mm
Y1	238 mm
Y2	171 mm

Technical Data

Attribute	Value
Suction rate (50 Hz)	25 m ³ /h
Rated power 50 Hz	0.75 kW
Weight	34.50 kg
Current type	AC3

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Vacuum pump

EVE-OG 25 AC3 F

Part no...:10.03.02.00020

<https://www.schmalz.com/10.03.02.00020>

Product family

EVE-OG

Accessories



OEL EVE-OG 1L ANDEROL 555

Part no...:27.02.01.00055

Construction use: Pump EVE-OG



VST EVE-OG-25-40

Part no...:10.03.02.00060

Construction use: Pump EVE-OG

Size: 25-40



ZUB EVE-OG Ölablass-Kit

Part no...:22.09.03.00038

Construction use: Pump EVE-OG

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es



Vacuum pump

EVE-OG 25 AC3 F

Part no...:10.03.02.00020

<https://www.schmalz.com/10.03.02.00020>

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Page 3 from 3