

Flat suction cup (round)

PFYN 60 VU1-72 G1/4-IG

Part no.:10.01.01.00609

<https://www.schmalz.com/10.01.01.00609>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups PFYN VU1 > PFYN 60 VU1-72 G1/4-IG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 60


Suction cup material: Vulkollan VU1

Material hardness [Shore A]: 72 Shore A

Nipple material: Aluminum

Connection: G1/4"-F

Design Data



Attribute	Value
Dmax(S)	67 mm
dn	3.50 mm
Ds	60 mm
G1	G1/4"-F
H	33.50 mm
LG1	12 mm
SW1	17 mm
Z (Stroke)	6 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Size	60
Suction cup material	Vulkollan VU1
Suction force (-600mbar)	130 N
Volume	15 cm ³
Curve radius (min) (convex)	75 mm
Hose diameter (rec.) d	6 mm
Nipple family	N 011

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Flat suction cup (round)

PFYN 60 VU1-72 G1/4-IG

Part no.:10.01.01.00609

<https://www.schmalz.com/10.01.01.00609>

Material hardness [Shore A]	72 Shore A
Weight	20.40 g
Number of folds	0
Product family	PFYN

Note: Permissible dimensional tolerances for elastomer parts according to DIN ISO 3302-1 M3

Spare parts



SA-NIP N011 G1/4-IG DN350

Part no.:10.01.01.00412

Nipple family: N 011

Thread G1: G1/4"-F

Length L1: 24.5 mm

Length L: 15 mm

Fitting length: 15 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum

Spanner size SW2: 5 mm



PFG 60 VU1-72 N011

Part no.:10.01.01.00606

Size: 60

Suction cup material: Vulkollan VU1

Material hardness [Shore A]: 72 Shore A

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Flat suction cup (round)

PFYN 60 VU1-72 G1/4-IG

Part no...:10.01.01.00609

<https://www.schmalz.com/10.01.01.00609>



PFG 60 VU1-72 N011

Part no...:10.01.01.00606

Size: 60

Suction cup material: Vulkollan VU1

Material hardness [Shore A]: 72 Shore A

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es