

Suction cup connection nipple

SA-NIP N005 G1/8-IG DN200

Part no.:10.01.01.03521

<https://www.schmalz.com/10.01.01.03521>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > SA-NIP N005 G1/8-IG DN200

Suction cup connection nipple



Nipple family: N 005

Thread G1: G1/8"-F

Length L1: 20.5 mm


Length L: 16 mm

Fitting length: 16 mm

Nominal diameter dn: 2 mm

Material: Aluminum

Design Data



Attribute	Value
dn	2 mm
D	8 mm
D2	5 mm
G1	G1/8"-F
L	16 mm
L1	20.50 mm
L2	2.50 mm
L3	2 mm
LG1	9 mm
SW1	14 mm

Technical Data

Attribute	Value
Nipple family	N 005
Material	Aluminum
Weight	5.30 g

Accessories

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Suction cup connection nipple

SA-NIP N005 G1/8-IG DN200

Part no...:10.01.01.03521

<https://www.schmalz.com/10.01.01.03521>



PFG 15 FPM-65 N005

Part no...:10.01.01.00071

Size: 15

Suction cup material: Fluorocautchuc FPM

Material hardness [Shore A]: 65 Shore A

Material property: non-marking



PFG 15 HT1-60 N005

Part no...:10.01.01.11162

Size: 15

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Material property: non-marking



PFG 15 NBR-CO-55 N005

Part no...:10.01.01.10067

Size: 15

Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Suction cup connection nipple

SA-NIP N005 G1/8-IG DN200

Part no...:10.01.01.03521

<https://www.schmalz.com/10.01.01.03521>



PFG 15 NBR-55 N005

Part no...:10.01.01.00011

Size: 15

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A



PFG 15 PU-55 N005

Part no...:10.01.01.00051

Size: 15

Suction cup material: Polyurethane PU

Material hardness [Shore A]: 55 Shore A



PFG 15 SI-CO-55 N005

Part no...:10.01.01.00627

Size: 15

Suction cup material: Silicone SI conductive

Material hardness [Shore A]: 55 Shore A

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Suction cup connection nipple

SA-NIP N005 G1/8-IG DN200

Part no...:10.01.01.03521

<https://www.schmalz.com/10.01.01.03521>



PFG 15 SI-55 N005

Part no...:10.01.01.00031

Size: 15

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es