

Vacuum block

VCBL-S4 120x50x50 D-360 TV

Part no.:10.01.12.01474

<https://www.schmalz.com/10.01.12.01474>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Systems from SCM / Morbidelli > Vacuum Blocks VCBL-S4 > VCBL-S4 120x50x50 D-360 TV

Vacuum block for SCM/Morbidelli console - Type 4



Dimensions (LxB): 120 x 50

Length L: 120 mm


Width B: 50 mm

Height H: 50 mm

Arrangement: Can be turned 360°

Add. function: Sensing valve

Design Data



Attribute	Value
B	50 mm
B1	145 mm
H	50 mm
H2	34 mm
L	120 mm
L1	145 mm
L2	109 mm
R1	413 mm

Technical Data

Attribute	Value
Weight	0.70 kg

Spare parts

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Vacuum block

VCBL-S4 120x50x50 D-360 TV

Part no...:10.01.12.01474

<https://www.schmalz.com/10.01.12.01474>



VCSP-O 140x130x16.5 TPE

Part no...:10.01.12.02325

Construction use: Vacuum block

Length L: 140 mm

Width B: 130 mm

Height H: 16.5 mm



TV D9 4.3

Part no...:10.01.12.02514

External diameter D: 9 mm

Spring stroke Z: 4.3 mm

Length L: 22.8 mm



TV D9 4.3

Part no...:10.01.12.02514

External diameter D: 9 mm

Spring stroke Z: 4.3 mm

Length L: 22.8 mm

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es

Vacuum block

VCBL-S4 120x50x50 D-360 TV

Part no...:10.01.12.01474

<https://www.schmalz.com/10.01.12.01474>




VCSP-O 120x50x15.5 TPE

Part no...:10.01.12.00012

Length L: 120 mm

Width B: 50 mm

Height H: 15.5 mm



VST VCBL-S DI-RA

Part no...:10.01.12.03318

Construction use: Vacuum block VCBL-S

Clamping range: mm

Contact Schmalz

Schmalz S.A. | Avda. Ribera de Axpe. 49, P.A.E. UDONDO-Edificio B-Nave 2, 48950 Erandio (Vizcaya), Spain | +34 94 4805585 | schmalz@schmalz.es