

Vacuum block

VCBL-S4 125x75x50 D-360 TV

Part no.:10.01.12.01473

<https://www.schmalz.com/10.01.12.01473>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Systems from SCM / Morbidelli > Vacuum Blocks VCBL-S4 > VCBL-S4 125x75x50 D-360 TV

Vacuum block for SCM/Morbidelli console - Type 4



Dimensions (LxB): 125 x 75

Length L: 125 mm


Width B: 75 mm

Height H: 50 mm

Arrangement: Can be turned 360°

Add. function: Sensing valve

Design Data



Attribute	Value
B	75 mm
B1	145 mm
H	50 mm
H2	34 mm
L	125 mm
L1	145 mm
L2	109 mm
R1	223 mm

Technical Data

Attribute	Value
Weight	0.80 kg

Accessories

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Vacuum block

VCBL-S4 125x75x50 D-360 TV

Part no.:10.01.12.01473

<https://www.schmalz.com/10.01.12.01473>



VCSP-O 125x75x17.7 MOS TPE

Part no.:10.01.12.03511

Construction use: Vacuum block

Length L: 125 mm

Width B: 75 mm

Height H: 17.7 mm

Add. function: Sealing lip with MOS

Spare parts



VCSP-O 140x130x16.5 TPE

Part no.:10.01.12.02325

Construction use: Vacuum block

Length L: 140 mm

Width B: 130 mm

Height H: 16.5 mm



TV D9 4.3

Part no.:10.01.12.02514

External diameter D: 9 mm

Spring stroke Z: 4.3 mm

Length L: 22.8 mm

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Vacuum block

VCBL-S4 125x75x50 D-360 TV

Part no...:10.01.12.01473

<https://www.schmalz.com/10.01.12.01473>



VCSP-O 125x75x16.5 TPE

Part no...:10.01.12.00011

Length L: 125 mm

Width B: 75 mm

Height H: 16.5 mm



TV D9 4.3

Part no...:10.01.12.02514

External diameter D: 9 mm

Spring stroke Z: 4.3 mm

Length L: 22.8 mm



VCDR 141x77.4x3 VCBL-S

Part no...:10.01.14.00235

Length L: 141 mm

Width B: 77.4 mm

Height H: 3 mm

Construction use: Vacuum block VCBL-S

Clamping range: mm

Contact Schmalz

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi