

Vacuum block

VCBL-S1 120x50x32.7 TV

Part no.:10.01.12.02319

<https://www.schmalz.com/10.01.12.02319>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Systems from SCM / Morbidelli > Vacuum Blocks VCBL-S1 > VCBL-S1 120x50x32.7 TV

Vacuum block for SCM/Morbidelli console - Type 1



Dimensions (LxB): 120 x 50

Length L: 120 mm

Width B: 50 mm

Height H: 32.7 mm

Add. function: Sensing valve

Design Data



Attribute	Value
B	50 mm
B1	120 mm
L	120 mm
H	32.70 mm
H2	20 mm
L1	120 mm
L2	72.50 mm

Technical Data

Attribute	Value
Weight	0.31 kg

Spare parts

Contact Schmalz


Schmalz UK Limited | Unit 2 Woodrow Business Centre, Woodrow Way, Irlam, Manchester M44 6NN, Great Britain | +44 161 243 4642 | Page 1 from 3
schmalz@schmalz.co.uk

Vacuum block

VCBL-S1 120x50x32.7 TV

Part no...:10.01.12.02319

<https://www.schmalz.com/10.01.12.02319>



VST VCBL-S DI-RA

Part no...:10.01.12.03573

Construction use: Vacuum block VCBL-S

Clamping range: mm




TV D9 4.3

Part no...:10.01.12.02514

External diameter D: 9 mm

Spring stroke Z: 4.3 mm

Length L: 22.8 mm



VCDR 115.5x43x5 VCBL-S

Part no...:10.01.12.03569

Length L: 115.5 mm

Width B: 43 mm

Height H: 5 mm

Construction use: Vacuum block VCBL-S

Clamping range: mm

Contact Schmalz

Schmalz UK Limited | Unit 2 Woodrow Business Centre, Woodrow Way, Irlam, Manchester M44 6NN, Great Britain | +44 161 243 4642 | Page 2 from 3
schmalz@schmalz.co.uk

Vacuum block

VCBL-S1 120x50x32.7 TV

Part no...:10.01.12.02319

<https://www.schmalz.com/10.01.12.02319>



VCSP-O 120x50x15.5 TPE

Part no...:10.01.12.00012

Length L: 120 mm

Width B: 50 mm

Height H: 15.5 mm



TV D9 4.3

Part no...:10.01.12.02514

External diameter D: 9 mm

Spring stroke Z: 4.3 mm

Length L: 22.8 mm

Contact Schmalz

Schmalz UK Limited | Unit 2 Woodrow Business Centre, Woodrow Way, Irlam, Manchester M44 6NN, Great Britain | +44 161 243 4642 | Page 3 from 3
schmalz@schmalz.co.uk