Vacuum pump

EVE-OG 255 AC3 F

Part no..:10.03.02.00052

https://www.schmalz.com/10.03.02.00052


Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Pumps > Oil-Lubricated Vacuum Pumps EVE-OG > EVE-OG 255 AC3 F

Oil-lubricated pump for maximum vacuum levels, requires little maintenance



- Current type: three-phase current
- Sound level at 50 Hz: 72 dB(A)
- with: Filter
- Suction rate (50 Hz): 255 m³/h
- Rated power 50 Hz: 5.5 kW
- Weight: 199.8 kg

Design Data



Attribute	Value
B	554 mm
B2	54 mm
G2	G2-1/2-F
G3	G2-F
G5	M10-F
H	410 mm
H1	680 mm
H2	240 mm
L	1056 mm
L2	293 mm
X1	303 mm
X2	390 mm
Y1	350 mm

Technical Data

Attribute	Value
Max. vacuum	-980 mbar
Max. vacuum	-28.94 inHg
Suction rate (50 Hz)	255 m³/h
Rated power 50 Hz	5.50 kW

Vacuum pump

EVE-OG 255 AC3 F

Part no..:10.03.02.00052

https://www.schmalz.com/10.03.02.00052

Sound level at 50 Hz	72 dB(A)
Weight	199.80 kg
Protection type IP	IP 54
Current type	AC3
Product family	EVE-OG

Accessories



DRM 40 P1 H

Part no..:10.07.02.00051

External diameter D: 40 mm
Measuring range: 0,0 ... 1,0 bar
Construction shape manometers: Connection at rear
Thread G1: G1"-M



MSS-K 10-16A

Part no..:10.04.04.00124

Construction use: PKZM0
Protection type IP: IP 65
Measuring range: bar

Vacuum pump

EVE-OG 255 AC3 F

Part no..:10.03.02.00052

https://www.schmalz.com/10.03.02.00052



OEL EVE-OG 1L ANDEROL 555

Part no..:27.02.01.00055

Construction use: Pump EVE-OG



OEL EVE-OG 5L ANDEROL 555

Part no..:27.02.01.00056

Construction use: Pump EVE-OG



ZUB EVE-OG Ölablass-Kit

Part no..:22.09.03.00038

Construction use: Pump EVE-OG

Spare parts

Vacuum pump

EVE-OG 255 AC3 F

Part no..:10.03.02.00052

https://www.schmalz.com/10.03.02.00052



FILT-EINS 3 150x222 PAP STF-2-1/2-IG

Part no..:10.07.01.00020

Filter pore size: 3 µm
External diameter D: 150 mm
Length L: 222 mm
Filter material: Paper
Construction use: Dust filter STF
Size: 2-1/2-IG



VST EVE-OG-165-255

Part no..:10.03.02.00057

Construction use: Pump EVE-OG
Size: 165-255