

## Suction cup connection nipple

SA-NIP N006 G1/8-IG DN200

Part no.:10.01.01.03522

<https://www.schmalz.com/10.01.01.03522>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > SA-NIP N006 G1/8-IG DN200

### Suction cup connection nipple




Thread G1: G1/8"-F

Length L1: 22.5 mm

Fitting length: 16 mm

Material: Aluminum

### Design Data



| Attribute | Value    |
|-----------|----------|
| D         | 10 mm    |
| dn        | 2 mm     |
| D2        | 5 mm     |
| G1        | G1/8"-F  |
| L         | 16 mm    |
| L1        | 22.50 mm |
| L2        | 4.50 mm  |
| L3        | 2 mm     |
| LG1       | 9 mm     |
| SW1       | 14 mm    |

### Technical Data

| Attribute     | Value    |
|---------------|----------|
| Nipple family | N 006    |
| Material      | Aluminum |
| Weight        | 5.60 g   |

### Accessories

#### Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | [schmalz@schmalz.co.in](mailto:schmalz@schmalz.co.in)

## Suction cup connection nipple

SA-NIP N006 G1/8-IG DN200

Part no...:10.01.01.03522

<https://www.schmalz.com/10.01.01.03522>



### PFG 20 FPM-65 N006


Part no...:10.01.01.00072

Size: 20

Suction cup material: Fluorocautchuc FPM

Material hardness [Shore A]: 65 Shore A

Material property: non-marking



### PFG 20 HT1-60 N006

Part no...:10.01.01.11163

Size: 20

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Material property: non-marking



### PFG 20 NBR-CO-55 N006

Part no...:10.01.01.10337

Size: 20

Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A

## Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | [schmalz@schmalz.co.in](mailto:schmalz@schmalz.co.in)

## Suction cup connection nipple

SA-NIP N006 G1/8-IG DN200

Part no...:10.01.01.03522

<https://www.schmalz.com/10.01.01.03522>



### PFG 20 NBR-55 N006

Part no...:10.01.01.00012

Size: 20

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Material characteristics: CSA



### PFG 20 PU-55 N006

Part no...:10.01.01.00052

Size: 20

Suction cup material: Polyurethane PU

Material hardness [Shore A]: 55 Shore A



### PFG 20 SI-55 N006

Part no...:10.01.01.00032

Size: 20

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

## Contact Schmalz

Schmalz India Pvt. Ltd. | EL - 38 J Block MIDC, 411 026 Bhosari, Pune, India | +91 20 691155-00 | [schmalz@schmalz.co.in](mailto:schmalz@schmalz.co.in)